



## 12 Month / 1000 Hour Limited Warranty

**This warranty applies to Global Industrial Model # 988993**

### Warranty Coverage

**Twelve (12) months** / 365 Days coverage limited to 1,000 Hours (whichever occurs first) for all frame, weldments and power train components. This is a parts only warranty. Labor is covered for the first six months/180 days from purchase.

**Six (6) months** / 180 Days parts and labor coverage limited to 1000 Hours (whichever occurs first) for all other parts excluding wearable items.

### Battery and Charger Coverage

Absorbed Glass Mat (AGM) batteries and built in chargers will be covered for (6) months / 180 days and will include replacement parts and labor coverage.

Warranty does not apply to NON Global Industrial attachments, battery packs, batteries and onboard chargers.

### Coverage

Global Industrial will repair or at its sole option substitute with new or remanufactured parts any item that may have failed due to a defect in material and/or workmanship that is covered under this warranty. All parts replaced under warranty must be Global Industrial OEM replacement parts. All warranty work must be performed by an Authorized Global Industrial distributor during normal business hours. Defective parts removed under this warranty period are the property of Global Industrial. Warranty issues/claims will not be authorized if required parts are not returned. Warranty is void if equipment is used in brine, corrosive or excessive moisture conditions or outside use.

### Limitations

The warranties contained herein shall not apply to or include: (a) periodic and / or normal maintenance outlined in the Operation and Service Maintenance Manual including but not limited to filters, adjustments or lubricants. (b) normal wear items including but not limited to hoses, fuses, bearings, leaks, seals and O-rings and tires. (c) accidents and abuse including but not limited to storage and fire. (d)

excessive exposure to salt, brine, acid, heat, cold, excessive moisture and other adverse environmental conditions. (e) improper maintenance, alterations or modifications not approved in writing by Global Industrial. (f) warranty work performed by a non-authorized Global Industrial distributor. (g) non-OEM Global Industrial parts installed during the warranty period. (h) this warranty does not apply to attachments not manufactured by Global Industrial. The warranties herein shall be void if (a) the hour meter or data plate has been altered or tampered with. (b) the equipment is not serviced according to the maintenance schedule found in the Operation and Service Manual.

### Limited Remedy

The remedy under the warranties herein is limited solely to the repair of defects in material and / or workmanship by an authorized Global Industrial distributor. Global Industrial is not responsible for rentals, loaners, overtime or cartage of equipment. Global Industrial will not be liable for incidental or consequential damage such as the inconvenience or loss of use of the Global Industrial trucks to the user resulting from the breach of written warranty or any implied warranty.

*The manufacturer reserves the right to make product improvements or changes but shall not incur responsibility to incorporate such product improvements or changes in any products previously shipped or currently in service.*

**THE WARRANTIES CONTAINED HEREIN ARE EXPRESSLY IN LIEU OF ALL OTHER WARRANTIES, EXPRESSED OR IMPLIED. INCLUDING WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE AND OF ANY OTHER OBLIGATION OR LIABILITY ON THE PART OF GLOBAL INDUSTRIAL INCLUDING EXPENSE, LOSS OR DAMAGE WHETHER DIRECT, INCIDENTAL, CONSEQUENTIAL, OR EXEMPLARY, ARISING IN CONNECTION WITH THE SALE OR USE OR INABILITY TO USE THE GLOBAL TRUCK FOR ANY PURPOSE.**

