

# 140 FC-i WELDER

ITEM# 261	Processes	Input Power	Rated Output	Amperage Range	Wire Diameter	Plate Thickness Range	Weight	Dimensions
<b>QUICK SPECS</b>	Flux Cored (FCAW)	120V	140A	140A	Up to .030"	Up to 1/4"	19 lbs.	16.75" x 8.125" x 12"



## FEATURES AND BENEFITS:

- Easy to use
- Portable
- No gas required
- Plate thickness range up to 1/4"
- Infinite voltage and wire feed speed control
- 120V input (20A/15A)
- 140A output

**Forney**  
**EASY WELD™**



### SPECIFICATIONS:

- 140A output; 120V input
- Recommended wire diameter: .030"
- Plate thickness range: Up to 1/4"
- Weight: 19 lbs.
- Dimensions: 16.75" X 8.125" X 12"

### FEATURES:

- Easy to use
- Portable
- No gas required
- Torch wrap
- Infinite voltage and wire feed speed control

### INCLUDES:

- 8' MIG gun
- 8' ground clamp
- 20A - 15A adapter

### APPLICATION:

- Do-it-yourself
- Maintenance & repair
- Metal fabrication
- Hobbyist

### WARRANTY:

- 6 month warranty

# Forney EASY WELD

## USE WITH FORNEY CONSUMABLES:



	ITEM#	DESCRIPTION
#1	85336	Tweco® style nozzle (21-50)
#2	60170	Tweco® style contact tip .024"
#2	60171	Tweco® style contact tip .030"
#2	60172	Tweco® style contact tip .035"
#3	85339	Tweco® style diffuser

## ACCESSORIES:

Portable Welding  
Cart  
ITEM# 332



E71T-GS Flux Cored MIG Wire  
ITEM# 42301 - .030" x 10 lb  
ITEM# 42303 - .035" x 10 lb



E71T-GS Flux Cored MIG Wire  
ITEM# 42300 - .030" x 2 lb  
ITEM# 42302 - .035" x 2 lb



Nozzle Gel  
16 oz.  
ITEM# 37031



Anti-Spatter  
16 oz.  
ITEM# 37030



Chipping Hammer  
Spring Handle  
ITEM# 70600



MIG Pliers  
7-in-1  
ITEM# 85801



Gray Leather  
Welding Gloves  
ITEM# 55200



Bandit Welding Helmet  
2" X 4-1/4"  
ITEM# 55666



Premier Series™ ADF Welding Helmet  
5.97" Square  
ITEM# 55701



SEE OUR  
FULL LINE OF  
METALWORKING ACCESSORIES