



# Chill-Its® #6215

PHASE CHANGE COOLING VEST >>>

6215 / 6215HV

FR FLAME RESISTANT

**TECH TAGS:**



Premium Phase Change Vest: Constant 58°F keeps workers cooler, safer, and more productive while providing FR protection.

- Maintains constant 58°F / 14°C
- Cooling lifecycle lasts up to 4 hours
- Comfortable cotton construction with hook & loop closure
- Extended vest surface area to enhance cooling power
- Modacrylic cotton blend FR fabric
- Fabric meets ASTM F1506 performance requirements (ATPV rating of 7.1 cal/cm<sup>2</sup>); classified CAT1 per NFPA 70E
- Non-toxic, non-carcinogenic, dialectic substance
- Elastic pen loop
- 6215HV designed with reflective accents for visibility
- Sizing: S/M, L/XL



## ACTIVATING YOUR COOLING VEST

// Simply place two removable packs in freezer or ice bath for 2-5 minutes or until packs become solid. Although they are not ice packs and will not be cool to the touch, these packs will stay 58°F for up to 4 hours.



## 6215 / 6215HV / 6230 FEATURES

- // Phase change packs maintain 58°F.
- // FR protection (6215 / 6215HV): The vest itself is made of a modacrylic cotton blend fabric offering inherent FR protection and boasting an ATPV rating of 7.1 cal/cm<sup>2</sup>.
- // Design features adjustable hook and loop closures on both the shoulders and waist allowing for the ultimate in comfort.
- // **NEW** design features a shorter, wider vest addressing the core body zones for cooling while increasing mobility in the workplace.
- // New honeycomb pack design allows for better flexibility when activated.
- // Packs contain a petroleum based, non-toxic cooling gel.
- // Extra cooling packs are available for purchase.

## ALSO AVAILABLE

- // 6230 Standard Phase Change Vest
- // 6240 Vest Extenders



**WWW.ERGODYNE.COM // 800 225 8238**