GLOBAL INDUSTRIAL
We can supply that.

MODEL NUMBER
412684

MOBILE ROBOT STRETCH WRAP MACHINE

SELF-PROPELLED & BATTERY-POWERED BY GLOBAL INDUSTRIAL™

The Global Industrial™ Mobile Robot Stretch Wrap Machine is your solution to wrapping pallets of any size anywhere throughout your facility.

Constructed from durable steel, this portable, battery-powered stretch wrap machine travels to your pallet, reducing forklift traffic and eliminating the need to transfer unstable loads to a fixed station. This versatile machine can run for 8 hours on a single charge, has no maximum weight capacity, and allows a single operator to wrap multiple pallets in different zones, freeing up manpower and increasing productivity. Ideal for use in warehouses, manufacturing settings, and more, this self-propelled unit comes equipped with three easy-to-steer wheels, a control panel with a colorful touchscreen, a belt-driving film carriage, a front safety bumper, and programmable wrap settings with film tension control for efficiently wrapping loads with minimal waste.

HIGHLIGHTS

- ✓ Slim profile takes up less space & easily navigates around your facility
- ✓ Ideal for oversized, unstable, and non-standard loads
- ✓ No maximum weight capacity

KEY FEATURES INCLUDE:

PROGRAMMABLE SETTINGS
Features programmable wrap settings with film tension control, allowing you to stretch film efficiently for maximum load security with minimal waste

HANDLES ANY SHAPE OR SIZE
Built for versatility, this powerful machine is perfect for irregular, extra-long, or non-standard pallets that can't be wrapped on traditional turntables

WRAP ANYWHERE
The mobile robot travels to your pallet, reducing forklift traffic and eliminating the need to transfer unstable or oversized loads to a fixed station

Durable steel construction

0-300% Stretch wrap ratio


Lead acid battery

Control panel with a colorful touchscreen

WEIGHT & DIMENSIONS

Length x Width x Height	69" x 46" x 88"
Weight	706 lbs.

Weight Cap.	No Limit
Max Film Diameter	10"
Max Wrap Height	84"
Max Roll Width	20"
Core Size	3"
Min. Roll Width	<20"

PRODUCT DETAILS

Battery Type	Lead Acid
Type	Semi-Automatic Portable Stretch Wrapper
Battery Included	Yes
Charging Amperage	15 A
Hertz	60
Voltage	110
Material	Steel
Color	Blue
Programmable	Yes
Travel Speed	262 ft/min.
Lift Speed	10-1/2 ft/min.
Warranty	Limited 1-Year