



HYDROMAX AIR COMPRESSOR

**2-STAGE, VARIABLE SPEED, 10HP, 80 GAL.,
1 & 3 PHASE, 208-230V BY GLOBAL INDUSTRIAL™**

Enhance your pneumatics system with the silent (63 dB at full operation) two-stage, variable speed HydroMax Air Compressor from Global Industrial™

Featuring a first-to-market closed system with a built-in radiator, this air compressor uses water to keep the pump cool during operation. Its soft-start variable speed motor is designed to reduce energy draw, greatly reducing operational expense. This product is WIFI enabled and allows you to use a smartphone to remotely monitor average energy draw, peak demand times, and even be notified of potential component issues & upcoming maintenance requirements. An ideal solution for commercial & industrial manufacturers, auto repair shops, small to mid-sized businesses, and more, this unit can connect multiple compressors in a daisy-chain methodology to ensure optimal pneumatic power. Limited 1-Year Warranty.

FEATURES INCLUDE:



FLEXIBLE OPERATION

Prewired for either single- or 3-phase operation to provide flexibility & possible energy cost savings



COMPRESSOR CAPACITY

Vertical 80-gallon 175 PSI ASME-certified tank



QUIET PERFORMANCE

Includes noise cancellation plates & (4) levels of air filtration to reduce DBA ratings up to 50%

WEIGHT & DIMENSIONS

| | |
|-----------|---------|
| Tank Size | 80 gal. |
|-----------|---------|

PRODUCT DETAILS

| | | | |
|------------------|----------------|------------------|----------------------------------|
| Oil Type | Synthetic | Material | Steel/Iron |
| Pump Drive | Belt | Phase | 1 & 3 |
| Oil System | Pressure Lube | Tank Orientation | Vertical |
| Air Dryer | No | Oil Sight Glass | Yes |
| Pump Material | Cast Iron | Pump RPM | 250-800 |
| Tank Drain Valve | Auto | Pump Type | Pressure Lubricated/Water Cooled |
| Max PSI | 175 PSI | CFM @ 90 PSI | 42 CFM |
| Start Type | Soft Draw | Low Oil Shutoff | Yes |
| Motor | WEG Industrial | Type | Variable Speed Reciprocating |
| CFM | 38 CFM | Style | Water Cooled Silent |
| Horsepower | 7.5 & 10HP | Air Filter | Yes |
| CFM @ 100 PSI | 38 CFM | Pre Filter | Yes |
| After Cooler | Yes | Noise Output | 63 dBA |



HIGHLIGHTS

- ✓ Soft-Start low energy draw variable speed motor
- ✓ WIFI operational control & monitoring
- ✓ Automotive "style" water-cooled system



Easy-to-read LCD screen that walks you through all of the compressor's features

Also available:

Model Number
133815, Silent 2-Stage
Variable Speed Air
Compressor, 10 HP, 80
Gal., 3-Phase, 460V

