

1. Identification:**Product Identity:** Splendor Floor finish**Recommended Use:** Water-borne floor polish**Producer / Distributor**Multi-Clean
600 Cardigan Road
Shoreview, MN 55126**Telephone Number for Information:** 651-481-1900**Emergency Telephone Number:** 800-255-3924**2. Hazard Identification:****Classification:****Health Class**

Mild Skin Irritation Category 3

Eye Irritant Category 2

Specific Target Organ Toxicity - Repeated Exposure Category 2

Physical Class**Environment Class****Label****Symbols****Signal Word** Warning**Hazard Statements:**

Causes mild skin irritation.

Causes eye irritation.

May cause damage to central nervous system, liver, and/or kidneys through prolonged or repeated exposure.

Precautionary Statements:

Do not breathe dust/fume/gas/mist/vapors/spray.

Wash hands thoroughly after handling.

If skin irritation occurs: Get medical attention.

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

If eye irritation persists: Get medical attention.

Get medical attention if you feel unwell.

Dispose of contents in accordance with local regulations.

3. Composition/Information on Ingredients

Ingredient	CAS Number	Percent by Weight
Emulsified Acrylic Polymers	Proprietary	10 - 30
Diethylene Glycol Monoethyl Ether	111-90-0	3 - 7
Tributoxyethyl Phosphate	78-51-3	1 - 5
Emulsified Polymer Wax	Proprietary	1 - 5
Water	7732-18-5	60 - 100

4. First-Aid Measures:**Ingestion:** If Swallowed: Do not induce vomiting. Drink water in large amounts and call a physician immediately. Never give anything by mouth to an unconscious person.**Eye Contact:** Flush eyes with running water for at least 15 minutes. If irritation persists, obtain medical attention.**Skin Contact:** Flush thoroughly with cool water. Remove and wash contaminated clothing before reuse.**Inhalation:** Move to fresh air.**5. Fire Fighting Measures:****Suitable Extinguishing Media:** Not Applicable**Special Fire Fighting Procedures:** Not Applicable**Unusual Fire and Explosion Hazards:** Not Applicable**6. Accidental Release Measures:**

Dike and contain spill with inert material (sand, earth, etc.). Collect spill with a mop, absorbent material (example: floor-dry) or vacuum. Thoroughly rinse affected area with water.

7. Handling and Storage:**Handling:** Keep from freezing. Keep out of reach of children.**Storage:** Maintain Temperature Minimum 40°F (4°C) - Maximum 100°F (38°C)

8. Exposure Controls / Personal Protection:**Exposure Limits:****Ingredients**

None Listed

CAS Number

XXXX

Osha PEL

XXX

ACGIH TLV

XXX

Exposure Controls:**Engineering Controls:** Normal good ventilation is sufficient**Personal Protective Equipment:****Eye Protection:** Approved Safety Goggles or Glasses**Skin Protection:** Chemical Resistant Rubber Gloves**Respiratory Protection:** Not required, Avoid breathing spray mist**9. Physical and Chemical Properties:****Physical State:** Liquid**pH:** 9 - 10**Appearance:** Milky White**Specific Gravity (H₂O = 1):** 1.031**Odor:** Mild Acrylic**Flammability:** None**Solubility:** Complete**Flash Point:** None**Evaporation Rate:** NA**Boiling Point:** > 212° F (100°C)**Vapor Pressure (MM HG):** NA**%volatile:** 81%**Vapor Density (Air = 1):** > 1**10. Stability and Reactivity:****Chemical Stability:** Stable**Possibility of Hazardous Reactions:** None are known**Incompatibility (Materials to Avoid):** None are known**Hazardous Decomposition or By-products:** None**Hazardous Polymerization:** Will not Occur**Conditions to Avoid:** None are known**11. Toxicological Information:****Signs and Symptoms of Overexposure:** Causes irritation on contact**Acute Effects:****Eye Contact:** Causes irritation on contact**Skin Contact:** Causes mild irritation on prolonged or repeated contact**Inhalation:** None Known**Ingestion:** May be harmful if swallowed**Target Organ Effects:** Central nervous system, Liver, Kidneys**Chronic Effects:** May cause damage to central nervous system, liver, and/or kidneys through prolonged or repeated exposure.**Acute Toxicity Values:****Oral LD₅₀** = > 5000 mg/kg**Dermal LD₅₀** = > 5000 mg/kg**Inhalation (Vapor) LC₅₀** = Vapors Considered Non**12. Ecological Information:****Persistence and Degradability:** Not Available**Bio Accumulative Potential:** Not Available**Mobility in Soil:** Not Available**Aquatic Toxicity:** Not Available**13. Disposal Considerations:**

Solution may contain zinc. For material not used in normal use, Coagulate with ferric chloride or sulfate and then lime. Decant the clear liquid to a sanitary sewer. Dispose of the coagulum by sanitary landfill or incinerator. Follow all existing pollution control ordinances.

14. Transportation Information:**UN Number:** None**Shipping Name:** Buffing or Polishing Compound**Transport Hazard Class:** None**Packing Group:** None**Marine Pollutant:** NO

15. Regulatory Information:

TSCA Status: All ingredients listed

Clean Water Act: None of the chemicals in this product are listed under the CWA

Clean Air Act: Glycol Ethers (Diethylene Glycol Monoethyl Ether(111-90-0)) is listed as a hazardous air pollutant (HAP)

CERCLA Reportable Quantity: None

SARA Title III Information:

Section 302 Extremely Hazardous Chemicals: None Listed

Section 311 / 312 Hazard Category: Immediate Health

Section 313 Toxic Chemicals: Glycol Ethers (Diethylene Glycol Monoethyl Ether (111-90-0))

State Regulations: None

International Regulations: WHMIS Controlled Product Hazard Class: D2B

16. Other Information:


Prepared By: Ron Camp

Telephone Number: 651-481-1900

Revision Date: 6/7/2013

Supersedes: 4/1/2012

The information contained herein is based on data considered accurate; however no warranty is expressed or implied regarding the accuracy of this data or the results to be obtained from the use thereof. The company assumes no responsibility for personal injury or property damage to vendees, users, or third parties caused by the material. Such vendees or users assume all risks associated with the use of the



Health	1
Flammability	0
Physical hazards	0