







80% AFUE SINGLE STAGE GAS FURNACE

MGM80S*A

MGD80S*A

A compact, easily maintained, affordable gas heating solution.

- Upflow / Horizontal & Downflow configurations
- 10-Year Parts / 20-Year Heat Exchanger Limited Warranty ‡

‡Warranty provides for a total of 10 years of limited warranty coverage (Standard 5-year limited parts warranty plus an additional 5-year limited extended parts warranty; 15-year for heat exchanger). Warranty must be registered online within 60 days of installation to qualify for extended coverage. Unregistered equipment defaults to 5-year coverage.

All units AHRI & CSA Design Certified

FEATURES & BENEFITS



Compact 33" height and standardized widths for easy coil fit



10-Year Parts / 20-Year Heat Exchanger Limited Waranty. ‡



MGM80S*A Upflow / Horizontal & MGD80S*A Downflow configurations



Self diagnostics saves last 5 fault codes regardless of power interruption



Optional LP & High Altitude Kits

- Multi-speed PSC blower motor
- Easily removable slide out blower design
- Single stage gas valve
- Rotatable draft inducer for venting flexibility
- Left or right utility connections
- Removable floor base for bottom return air
- Zero step horizontal conversion

