



Features:

- **FAST** testing measures in <1 second
- **PRECISE** infrared reading
- **SIMPLE** one button design
- **Automatic** mode switch between forehead and ear mode
- **Easy to read** LCD display with backlight and large font
- **Audio & visual** fever warning
- **Two temperature measurement modes** (people or objects) with automatic recognition
- **32 group memory**
- **User selectable** °F or °C
- **Includes a magnetic probe cover**
- **Auto-standby** after 10 seconds

Specifications Chart

Temperature Range:	94.1°-108.5°F (34.5°-42.5°C)
Power Supply:	DC 3V - 2 AAA batteries (not included)
Measuring Distance Range:	3/4" to 2"
Response Time:	<1 Second
Memory Data:	32 Records
High-Fever Warning:	Audio and Visual
Display:	LCD with Backlight
Measuring Unit:	°F or °C
Max. Allowable Error:	± 0.3°F (0.2°C)
Temperature Resolution:	0.1°F / 0.1°C
Product Weight:	0.2 lbs. (excluding batteries)
Product Dimensions:	5.7"L x 2.0"W x 1.5"H
Certification:	FDA
Ambient Temp. Working Range:	60°-95°F (16°-35°C)