

Fingertip Pulse Oximeter Specifications

Model 436963



Features:

- *Horizontal screen design makes it easier to observe values*
- *Accurate measurement quickly measure the values in 8 seconds*
- *High definition OLED display screen*
- *Accommodates a wide range of finger sizes*
- *Lightweight and portable*
- *Carrying case and lanyard included*

Includes:

- *Fingertip Pulse Oximeter*
- *Carrying Case*
- *Lanyard*

Specifications Chart

Display Type:	OLED
SpO2 Measuring Range:	70-100%
SpO2 Display Resolution:	1%
SpO2 Accuracy Range:	±2%
Pulse Rate Measuring Range:	25-250 bpm
Pulse Rate Display Resolution:	1 bpm
Pulse Rate Accuracy Range:	±3 bpm
Pulse Intensity:	Pulse Wave Graph
Power Supply:	2 AAA batteries (not Included)
Net Weight:	0.06 lb.
Dimensions:	2.3" x 1.3" x 1.25"
Color:	White
Certifications:	CE & FDA
Limited Warranty:	1 Year