

Model 695749



Features:

- **Soft gum shell and flexible probe design**
- **Temperature display in °C or °F**
- **Large LCD Screen**
- **Waterproof and break-resistant**
- **Oral and axillary temperature taking options**
- **Beeper alarm function**
- **Auto shut-off**
- **Mercury free**
- **Convenient storage case**



Specifications Chart

Temperature Range:	89.6°F to 109.2°F (32.0°C to 42.9°C)
Accuracy:	±0.2°F (±0.1°C)
Measuring Time:	Oral: 30 seconds; Axillary: 60 seconds
Battery:	One 1.5V DC button battery (LR41)
Battery Life:	Approx. 200 hours
Memory Data:	Last reading
Dimensions:	4.9"L x 0.7"W x 0.4"H
Weight:	0.02 lb. (10g) including battery
Material:	ABS
Sensor Type:	Thermostat
Certification:	CE & FDA
Limited Warranty:	1 Year