

Model 708528: Counter Stand  
 Model 708529: 3'H Floor Mount  
 Model 708530: 4'H Floor Mount



## Features:

- **Ultra-thin 8" wide LCD screen**
- **Real time body temperature readings**
- **Face recognition; supports 50,000 user faces**
- **Mask recognition**
- **Accuracy:  $\pm 0.5^{\circ}\text{F}$**
- **Elevated temperature detection with alarm**
- **Records facial identification and temperature information**
- **Available in 3 different size mounting stands**
- **Built-in WiFi module, can be used as hotspot and WiFi connection.**
- **Great for use in areas including hotels, office buildings, schools, entrance gates, and other areas where face access control is required**

Computer Requirements: Windows 7/8/9/10

## Specifications:

Sensor:	Thermal Imaging Infrared Temperature Sensor
Temperature Range:	95 - 108°F; $\pm 0.5^{\circ}$ (35 - 42°C; $\pm 0.3^{\circ}$ )
Display:	8" LCD
Recognition Distance:	1.6 to 16 ft.
Response Time:	$\leq 0.3$ Second
Memory Data:	30,000 Faces
Camera:	2 MP
Lens:	1:2.8, Focal Length .07", Field of View: 118°
Dynamic:	$\geq 105\text{dB}$
Signal to Noise Ratio:	$\geq 35\text{dB}$
White Balance:	Auto, Indoor, Outdoor, Sodium Lamp Mode, Manual
Video:	H.265 Main Profile / H.264 High profile / M-JPEG
Max Resolution:	800 x 1280 @ 30fps
Output Bit Rate:	Auto, Indoor, Outdoor, Sodium Lamp Mode, Manual
Audio Compression:	G711, PCM
USB Interface:	(1) USB
Device Storage:	8G
Power:	DC12V 2A
Interfaces:	Rich Hardware, Integrated 100M Ethernet, Audio, Wiegand, Relay, USB
Mounting Stand Options:	Counter Stand, 3'H Mount or 4'H Mount
Connection:	Ethernet, Wifi, Hotspot
Operating System:	Linux OS
Recording Capacity:	5 million
Product Dimensions:	9-1/2" x 5-1/3" x 1"
Weight:	2 lbs.



Model 708528



Model 708529



Model 708530