

## ST-THERMSCAN-1

### SecurityTronix ThermScan™ Wall Mounted Non-Contact Forehead Thermometer

The SecurityTronix ThermScan™ accurately and instantly scans the forehead and alerts by alarm if an elevated skin temperature is detected. Quickly get compliant with temperature screening at your place of business.

The intent is not to diagnose, but to raise awareness so people can get a proper assessment before fully entering the business.



- Lower cost than thermal cameras
- Highly accurate
- Quick and easy to install
- Alarm function
- Contactless
- Reduces usage of PPE for manual scanning
- Quick automatic measurement
- Cost-effective, even for small businesses

#### Key Features

- Detects surface skin temperature without any contact
- Quickly detects surface temperature in less than one second response time
- Alarm alerts if surface skin temperature detected is higher than 99.1°F (37.3°C)
- Digital display

#### Installation

- Can be mounted with screws (included), double sided tape (included), or on a tripod



#### Specifications

|   |                                      |                            |  |
|---|--------------------------------------|----------------------------|--|
| <b>Temperature Measurement Distance</b> | 2" - 4" (5 - 10 cm)                  | <b>Power Consumption</b>   | Less than 3W                                 |
| <b>Temperature Measurement Accuracy</b> | ± 0.4°F (± 0.2°C)                    | <b>Operating Humidity</b>  | 95%, non-condensing                          |
| <b>Testing Temperature Range</b>        | 32 - 122°F (0-50°C)                  | <b>Working Temperature</b> | 50 - 104°F (10 - 40°C)                       |
| <b>Temperature Measurement Speed</b>    | Less than 1 second                   | <b>Product Weight</b>      | 0.77lbs (350g)                               |
| <b>Abnormal Temperature Alert</b>       | Yes                                  | <b>Product Dimension</b>   | 6.69" x 4.52" x 5.51"<br>(170 x 115 x 140mm) |
| <b>Working Voltage</b>                  | USB - DC 5V<br>Power supply included | <b>Bracket</b>             | Wall Mount                                   |
| <b>External Power Supply</b>            | AC 100/60Hz                          | <b>Rating</b>              | FCC, RoHS, CE                                |