



DYNAMIC

HIGH DENSITY

STORAGE

FOR FASTER

EACH PICKS

Pick Smarter. Pick Better. Pick UNEX.



Maximize Warehouse Space

Maximize warehouse space, pick orders faster and increase accuracy with SpeedCell® - a dynamic, high-density storage solution uniquely designed to save time, space, and money by using existing space within standard pallet racking.

SpeedCell can compress 200' of rack or shelving into 40' of highly organized space. More pick facings and greater SKU density equates to less travel time and less seek time while pulling orders and restocking locations.

Columns made of high-strength industrial textiles won't mold or rust and are fire/flame resistant. Columns are suspended from the patented* steel track system which is made from pre-galvanized steel that integrates into any type of pallet rack beams.

SpeedCell®

- **Increases storage density by 40-60%**
- **Reduces labor costs up to 40%**
- **Transforms space into useable storage**
- **More SKUs | Less Space | Greater Efficiency**

Each "Cell" has a unique location label holder making it easy to locate your product whether using basic paper picking methodology or advanced WMS/WCS for non-directed and/or directed put away & picking. Columns easily slide side-to-side to gain access to rear columns. Each location is ergonomically designed to reduce the need for deep bending, stretching or step stools.

Features

- Designs can range from 1-3 rows deep, up to 12 columns wide (144" wide bays)
- Ergonomically designed
- Operating temperature of -20°- 180°F (-29°- 82°C)
- Resistant to: fire/flame & mold
- Storage Capacity:
Cell: Up to 35 lbs
Column: Up to 240 lbs

*PATENT # 8.827.090

Pre-Configured Bays



PART NUMBER EXAMPLE - SPEEDCELL BAY

SCB	96	3	21	126	L4	F
SERIES	WIDTH	ROWS DEEP	COLUMNS	LOCATIONS	4" FRONT LIP	FULL CLOSED BACK

Standard Suspension System

- Suspended within selective rack or wide span rack system
- Fits within any type of beam: box, structural, or step; pick modules and mezzanines
- Static or dynamic: designs can range from 1-3 rows in depth


SPEEDCELL COLUMN MATERIAL	
WEIGHT	13 oz
DENIER	1000
FMVSS 302 FLAME RESIST	PASS
TREATMENT	ANTI-MILDEW
CA FIRE CODE COMPLIANT	YES
CAPACITY PER COLUMN	240 lb
CAPACITY PER CELL	35 lb
COLOR	FROST WHITE

PART NUMBER EXAMPLE - SPEEDCELL COLUMNS								
SC	78	18	12	OP	S	W	04	CD
SERIES	HEIGHT	WIDTH	DEPTH	FRONT	BACK	COLOR	CELLS	COLLAPSIBLE DIVIDER


AVAILABLE SIZES: SPEEDCELL COLUMNS	
WIDTHS	12", 18" & 24"
DEPTHS	12" & 19"
CELLS PER COLUMN	4 - 12

STANDARD LIP HEIGHT	
4 - 9 CELLS	4"
10 - 12 CELLS	2.5"

Front Styles




Open Label: Roof



Open Label: Shelf



Lip Label: Center



Lip Vertical Divider Label: (2) Lip


Back Styles



Back: (1) V-Strap



Back: (2) V-Strap



Back: Closed

SpeedCartt™

Mobilize Your Picking Process

with a flexible, mobile solution for restocking, order fulfillment, seasonal demands, and more! Constructed from the same lightweight, yet heavy-duty materials as standard SpeedCell storage solutions, our mobile SpeedCartt is designed for years of low-maintenance, demanding warehouse environment use.

Configurations for single-side or back-to-back loading for greater SKU accessibility are available.



AVAILABLE SIZES: CART	
WIDTHS	18" & 24"
DEPTHS	48" & 60"
AVAILABLE SIZES: COLUMNS	
WIDTHS	11" & 14"
DEPTHS	9", 12", 18" & 24"

PART NUMBER EXAMPLE - SPEEDCARTT			
SCRT	2460	B2B	40
SPEEDCELL CART	24X60	BACK TO BACK	40 CELLS



UNEX MANUFACTURING, INC. | 691 New Hampshire Avenue, Lakewood, NJ 08701
800.695.SPAN (7726) 732-928-2800 | fax: 732-928-2828 | e-mail: span@unex.com

