

# 34" High Velocity Fan



## YM-Yoke Mount Standard Mounting Options



PB- Pedestal Base

Column Wall Mount Available

Shipping Weights:

240 lbs/ 108.8kg

| SIZE | CFM    | HP | FAN DIMENSIONS |       |        | DISTANCE<br>AIR THROW | SHIPPING<br>WEIGHT |
|------|--------|----|----------------|-------|--------|-----------------------|--------------------|
|      |        |    | W              | D     | I.D.   |                       |                    |
| 34"  | 17,000 | 3  | 43.5"          | 25.5" | 34.9 " | 230' / 70.1 m         | 215 lbs/ 104.3kg   |

**Propeller:** 34" Diameter, 4 Blade GalvAlum (15 Degree)

**Fan Inlet/Outlet:** 14 Gauge Spun Steel

**Finger Guards:** OSHA Standard, Spiral Wound Steel

**RPM:** 1200

**Decibels:** 88 @ 20'

**Enclosure:** TEAO Standard

**Frame:** 56

**Ambient Temperature:** 40C

**Duty Cycle:** Continuous

**Power Cord:** N/A

**Coverage:** 17,000 Sq.Ft. Max

**Warranty:** 2 Years

| Voltage        | Motor<br>Amps | Running<br>Amps |
|----------------|---------------|-----------------|
| 208-230/ 460V* | 9.9-9.2/ 4.6  | 9.7-9.0/ 4.5    |

\* Standard

34 " High Velocity Fan Air Flow Pattern

