

ENERGY SAVE Oscillating Ceramic Heater



#CZ448E (120988)

- 3 heat settings plus fan-only setting
- ENERGY SAVE technology heats comfortably with 30% less energy
- Powerful ceramic PTC heating element
- Adjustable thermostat
- 70° oscillation for wide coverage
- Stay cool body with molded handle
- Safety tip-over switch
- Safety overheat protection system
- ETL approved for sale in the US & Canada
- Replaces CZ448

Specifications

Heater Type	Ceramic, Fan-Forced
Volts / Amps	120 VAC / 60 Hz / 12.5 A
Cord / Plug	5 ft. / Polarized
Watts	750 / 1500 Watts + Energy Save
BTUs	5120 BTUs
Item Dimensions	L- 6.25" x W- 5.13" x H- 10.25"
Box Dimensions	L- 6.60" x W- 5.60" x H- 11.10"
Box Cube	0.23'
Box Weight	3.59 lbs.
Item UPC	075877209887
MS Dimensions	L- 17.25" x W- 13.60" x H- 11.50"
MS Case Qty	6
MS Cube	1.56'
MS Weight	21.57 lbs.
MS I2of5 UPC	20075877209881
Pallet Qty	TBD
40' HQ Qty	8,544
Port	Shanghai

