

DATE: _____ LOCATION: _____
 TYPE: _____ PROJECT: _____
 CATALOG #: _____

tradeSELECT®

FEATURES

- 3,500 nominal lumens
- 116 lumens per watt
- 4000K CCT
- 0–10V dimming to 10%
- For use in a wide range of surface mount ceiling and wall applications
- Universal Voltage (120–277V)
- 80+ CRI
- Acrylic lens for superior efficiency and resistance to UV aging



SPECIFICATIONS

CONSTRUCTION

- Steel housing and polycarbonate end caps

OPTICS

- Frosted acrylic lens

INSTALLATION

- Fully assembled for quick installation
- Electrical access from middle exterior of fixture
- Refer to installation instructions for more detail

ELECTRICAL

- 54,000 hour LEDs at L70 for reduced maintenance
- Operates at 120–277V input
- 0–10V dimmable driver, down to 10%

CERTIFICATIONS

- All luminaires are built to UL 1598 standards and bear appropriate ETL labels

CERTIFICATIONS (CONTINUED)

- Damp location label standard
- Adheres to LM79, LM80, and TM21 industry standards for photometrics and lifetime calculations


WARRANTY

- 5 year warranty
- See [HLI Standard Warranty](#) for additional information

ORDERING GUIDE

Catalog Number	UPC	Description	Delivered Lumens	Watts	LPW
CNW4-3540	840141400235	4ft LED Narrow Wrap, 4000K, 0–10V Dimming	3507	30	116

DIMENSIONS



KEY DATA	
Lumens	3507
Wattage	30
Efficacy (LPW)	116
Reported Life (Hours)	L70/54,000

PHOTOMETRY

CNW4-3540

LUMINAIRE DATA

Test No.	23865
Description	CNW 4ft Narrow Wrap 4000K 3500lm
Delivered Lumens	3507
Watts	30
Efficacy	116.7
Mounting	Surface
Spacing Criterion	0° = N/A 90° = N/A

ZONAL LUMEN SUMMARY

Zone	Lumens	% Luminaire
0-30	1022	29.1
0-40	1637	46.7
0-60	2779	79.2
0-90	3483	99.3
0-180	3507	100.0

POLAR GRAPH

