

# Wash-Ware® 3401 Series

Elliptical Models - 1, 2 or 3 Stations



3402-2-F

Fixture May Show Some Available Options

Please visit **www.acorneng.com** for most current specifications.

## Elliptical Models - 1, 2 or 3 Stations

**Bowl** is 14 gage type 304 stainless steel with satin finish and has an integral backsplash and sprayhead. Heavy-duty S-clips securely anchor the backsplash to the wall. Sprayhead has self-draining, air-circulating soap holders.

**Standard Housing** is black vinylclad, galvanized steel. Base is heavy gage, type 304 stainless steel with satin finish.

**-1 Off-Floor Fixtures are ADA Compliant.** Off-floor sensor and hand-operated units conform to ANSI, UFAS and ADA requirements for accessibility. Compliance is subject to the interpretation and requirements of the local code authority.

**Sectional Control** is standard. One pushbutton or sensor actuates one station.

**Hand Pushbuttons** (suffix option -H) operate metering non-hold open Air-Control Valves and can be field set for flow ranging from 5 to 60 seconds.

**Electronic Sensor Operation** (suffix option -SO) includes individual solenoid valves activated by infrared sensors. A low voltage transformer is provided.

**Foot Pushbuttons** (suffix option -F) operate direct acting non-metering Air-Control Valves that permit the user to control the length of the washing cycle. This option not available with -1 Off-Floor fixture mounting and -ES series contoured base pedestal housing units. This option is not ADA compliant.

Spray Nozzles are vandal-resistant and provide a concentrated 0.5 GPM spray at each station.

**Hot & Cold Supplies** are blended in an ASSE 1070 compliant temperature/pressure balancing mixing valve with integral checks and strainers. A minimum of 30 PSI supply pressure is required.

**Waste Connection** is a 1-1/2" OD x 4" tailpiece.

### **GUIDE SPECIFICATION**


Provide and install Acorn Washfountain (specify model number and options) factory pre-assembled, with individual sectional control. Bowl shall be 14 gage stainless steel and shall have an integral backsplash with vandal-resistant spray nozzle(s) and 0.5 GPM flow control(s). Provide self-draining, air-circulating soap holders on top of sprayhead. On-Floor and Off-Floor Models shall have backsplash and housing framework anchored to wall. The wall shall be structurally reinforced to support the fixture. Standard base On-Floor Models shall have additional floor anchoring. Provide an ASSE 1070 compliant temperature/pressure balancing mixing valve with integral checks and strainers in H & C supply and field set water temperature at 105 degree Fahrenheit. When hand operated non-hold open metering valves are specified, timing cycle shall be field set for approximately (specify) seconds. Off-floor units to conform to ANSI, UFAS and ADA requirements for accessibility.

Page 1	W.3401	Revised: 03/04/22
--------	--------	-------------------

# Wash-Ware®: 3401 Elliptical Models -1, 2, or 3 Stations

#### **MODEL NUMBER AND OPTIONS SELECTION PRODUCT OPTIONS** ☐ -EG Enviro-Glaze Color, Bowl and Sprayhead **BASE MODEL NUMBERS (Must Specify)** Specify: Elliptical, One Station **3401** Hose Bibb, Specify: Left Side Right Side 🔲 -НВ Elliptical, Two Station **3402** (Not ADA Compliant.) **3403** Elliptical, Three Station ☐ -JH31 31" Junior Rim Height 🔲 -SPX FIXTURE MOUNTING AND WASTE (Must Specify) 16 Gage Stainless Steel Housing (1-1/2" OD Tailpiece Provided Standard) -ST Single Temperature Valve Off-Floor, Wall Outlet, ADA Compliant **-**1 **□**-2 On-Floor, Wall Outlet **OPERATION (Must Specify)** ☐ -F ☐ -H Foot Operation (-2 On-Floor Models Only) Hand Operation -PPZ Programmable Piezo Pushbutton Electronic Metering □ -SO Sensor Operation Sensor Operation (Batteries Not Included) ☐ -SO-BAT

Please visit  $\underline{\textit{www.acorneng.com}}$  for most current specifications.



Page 2 W.3401 Revised: 03/04/22

Quantity

Signature