


think MARVEL®

ISO 9001:2015 UL CERTIFIED
STORAGE TECHNICAL SPECIFICATIONS
Made in the U.S.A. - Greenguard Certified - Lifetime Warranty



FINISHES

- Powder coat; one of the most economical, color durable quality finishes
- 2 mm thick standard textured paint
- Textured powder coat finish inhibits rust; scratch & glare resistant
- Optional smooth finish available

ZAPF LATERAL FILES

- Two Lateral File Converters per Lateral File
- One Adjustable Hanger Bar per File Drawer
- Adjustable Slides
- Drawers hold suspended files in letter, A4 and legal sizes
- Can be converted to front-to-back filing with Lateral File Converters
- Interlocking system allows one drawer to be opened at a time
- Heights: 28"H, 40"H or 52"H
- Depth: 19"D
- Widths: 30"W, 36"W or 42"W



ENSEMBLE BOOKCASES

- 18 gauge cold rolled steel platform
- 20 gauge cold rolled steel frame
- 22 gauge cold rolled steel shelves
- Shelf adjustable range of 1/2"
- Load capacity of ?
- Interior dimensions of 33.5" Wx13.5"Dx36.5"H
- Outside dimension of 36"Wx14"
- Heights: 27"H, 40"H or 65"H



For more information Call Sales at 1.800.621.8846 or Email us at sales@marvelgroup.com



3843 West 43rd Street, Chicago, IL 60632
1.800.621.8846 | www.marvelgroup.com

