



OIL & GAS PRODUCT


PPE COLLECTION

PROTECTION · PRODUCTIVITY · ELEMENTS











WE LIVE TO MAKE IT

PROFLEX° TREX SICUILIERZ° GLOWEAR° ARSENAL



SAFER.

Since 1983, Ergodyne has pioneered the development of products that Make The Workplace A Betterplace™. Our line of top flight, battle-tested, Tenacious Work Gear® is precision crafted to provide protection, improve productivity and manage the elements for workers on jobsites the world over.



squids

CORE

Chill-Its SHAX

N-FERNO // BETENACIOUS //

LAME PROTECT

(BECAUSE FR GEAR DOESN'T HAVE TO SUCK.)

Workers on the Oil & Gas battlefield face the risk of fire and explosion every day due to ignition of flammable vapors or gases.* Proper and certified flame resistant PPE offer dual-hazard solutions for both flash fire and electrical arc flash applications. Don't worry, Ergodyne's superhero style and comfort come standard. *2014 Safety and Health Topics: Oil and Gas Extraction



Lightweight, ultra-soft mid-layer for enhanced comfort, breathability and fit. Dual hazard solution for both flash fire and arc flash applications.

Heavy-duty sweatshirts providing dual hazard protection for both arc flash and flash fires.

7445



8260FRHL & 8356FRHL // FR MODACRYLIC VESTS

ASTM F1506-certified modacrylic mesh fabric. Hook and loop closure and D-ring access.

7490 & 7490X // FR COVERALLS Cool, comfortable, and breathable

coverall that provides dual hazard FR protection.

SOLUTION>>>

ARC FLASH AND FLASH FIRE PROTECTION, VISIBILITY, REFLECTIVITY, AND MORE.





{YOU'VE GOT NO TIME FOR BUSTED KNUCKLES.}

Over 110,000 workers are sidelined by hand and finger injuries every year, so protecting your hands with a proper glove is mission critical. Unfortunately, most hand protection solutions only focus on the palm side of the hand — leaving the backside (or dorsal side) exposed to injury. *Bureau of Labor Statistics



925F(x) // ORIGINAL

Patented back-of-hand protection meets superior abrasion resistance, dexterity and grip.

925F(x)OD // OUTDRY®

Thermal waterproof dorsal impactreducing gloves w/OutDry.®





925F(x)CP // CUT, PUNCTURE

Dorsal impact protection with Level 3 cut protection and enhanced grip.



920 // NITRILE DIPPED

Patent-pending dorsal protection with the exceptional gripping of a foam nitrile palm.

924LD // LIGHT

Lighter dorsal impact protection with breathable Air-Mesh back.

SOLUTION>>>

MAXIMUM BACK-OF-HAND IMPACT PROTECTION; CUT, PUNCTURE, AND ABRASION RESISTANCE; DEXTERITY; GRIP AND MORE.



// OBJECTS AT HEIGHTS //

QUIT RAINING WRENCHES ON YOUR CO-WORKERS.

241 workers were killed by a falling object in 2012.* OSHA states that if you're working at heights, tools and equipment must be secured and properly stored. Period.**


*Bureau of Labor Statistics **OSHA Standards for General Industry





3703 // ELASTIC TOOL TAILS™

Provide retrofit attachment points for a variety of tools and equipment up to 15 lbs. when captured by a Squids $^{\mathbb{R}}$ Tool Trap $^{\mathbb{T}}$.



3540 // LARGE TIE HOOK

Heavy-duty, reusable locking tie hook for organizing.

3723 // COLD SHRINK TOOL TRAP™

Patent pending Shrink Trap captures Squids[®] Elastic Tool Tails[™] creating a retrofit attachment for tethering.



5518 // AERIAL TOOL POUCH

Loop design that easily attaches to any belt while keeping items secure.



SOLUTION>>>

ORGANIZE AND TETHER TOOLS//EQUIPMENT AS WELL AS PROVIDE SAFE TRANSPORT FOR OBJECTS TO AND FROM THE WORKZONE.



HEAT STRESS //

{WORKPLACE INFERNO — NO MORE!}

Whether always hot or suddenly getting hotter – many workzones are becoming dangerous heat zones. OSHA recently reported approximately 4,200 cases of injury and 53 deaths caused by extreme heat.* These numbers are shocking and unacceptable — especially when the cause of Heat Related Illness (HRI) is 100% preventable.

6710FR
6710FR
6700CT

6700FR & 6710FR & 6717FR // EVAPORATIVE

Activated polymers bring cooling relief along with FR protection.

6700FR

6700CT & 6602 // EVAPORATIVE

Advanced PVA material keeps you cool without the bulk.

6602



6200 // PHASE CHANGE

Constant 58° keeps workers cooler, safer and more productive. FR fabric vest.



5157 // PREMIUM CARGO HYDRATION PACK

Keep workers organized and hydrated with this unique cargo hydration pack.

SOLUTION>>>

EVAPORATIVE, ABSORPTIVE, PHASE CHANGE AND HYDRATING TECHNOLOGIES TO MITIGATE RISK OF HEAT STRESS.



COLD STRESS //

{TELL WINTER WEATHER, YOU'RE TOAST.}

It's hard to be productive and safe when you are shivering. If workers do not have proper protection, the body is unable to warm itself which can lead to serious cold-related illnesses, permanent tissue damage, or even death. Not to mention, 40% of the body's heat is lost through the head.* *OSHA Safety & Health Guides: Cold Stress



6872 & 6880 & 6882 // FR WINTER LINER

Inherent FR fabrics for lasting protection. Meets ASTM F1506.



6885 // TWO-WAY FR WINTER LINER

Versatile design with detachable upper and lower sections to provide the ultimate in winter and FR protection. Meets ASTM F1506.

6825 // NOMEX BALACLAVA

Keeps head and neck warm while providing FR protection with an ATPV value of 9.7 cal/cm2 (HRC 2).



6486 // FR MULTI-BAND

100% Nomex[®]. Supreme FR protection, warmth, and performance with a multitude of uses and ways to wear.

SOLUTION>>>


FR FABRICS AND SUPERIOR FEATURES FOR RELIABLE WARMTH AND PROTECTION.



// SLIPS, TRIPS, AND FALLS

{BIG STUDS AT WORK.}

In 2011, slips, trips, and falls accounted for 225,550 injuries—33.5% of which resulted in 31+ days away from work.* When terrain is a potential occupational hazard, footwear enhanced with a traction device provides workers with the grip they need. *2012 BLS table: R70



6300 // ICE TRACTION

One-piece ice traction device for shoes or boots, delivers tenacious grip and stability.



6315 // STRAP-ON HEEL ICE TRACTION

Rugged steel plates turn boot heels into ice picks, leaving the mid-foot free for vehicle operation.

6310 // ICE TRACTION

Adjustable one-piece ice traction that delivers tenacious grip, stability and reflectivity.

SOLUTION>>>

GRIP, STABILITY, REFLECTIVITY, AND MORE.





INTERGALACTIC
HEADQUARTERS:
44° 58' 18.31" N 93° 09' 12.88" W
ALT. 934 FT.
1021 BANDANA BOULEVARD EAST
SUITE 220
SAINT PAUL, MN, USA 55108
PHONE 651 642 9889 // 800 225 8238
WWW.ERGODYNE.COM

MEMBER ASSOCIATIONS:











©2014 Tenacious Holdings Inc. All Rights Reserved. All Wrongs Reversed. Ergodyne, Ergoman and Ergoman design, Tenacious Work Gear Logo, Ergodyne Tenacious Work Gear, Arsenal, Chill-Its, GloWear, Nuºo,, Squids, Sticky Fingers, ProFlex, CORE Performance Work Wear, N-Ferno, SHAX and Skullerz are registered trademarks of Ergodyne and protected in the U.S. and abroad. Be Tenacious, BET (Beverage Extrication Tool), Open-Center Stay, Perfor-air, Power Panel Positioner, Storm Drains, Products for Occupational Athletes, Trex, Hot Rox, Tenacious-U, and ZeroRebound, Lil' Buddies, Tenacious Testers, Tenacious Nation, Make the Workplace a Betterplace and Drops Free Zone are trademarks of Ergodyne. Trademarks of companies mentioned herein appear for identification purposes only and are the property of their respective companies. All other product names mentioned herein may be trademarks and/or registered trademarks of their respective owners. Products of Property of their Product National Constitution of Property of their Product National Property of their Product National Property of their Product National Product National