
SHORTY LIFT MASTER BOOM, TELESCOPING - LMS-EBT-46-4

APPROX WEIGHT: 267.26 lbs.

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE *** ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



DISTANCE	31"	37"	43"	52 3/4"	66"	79 1/4"	90 3/8"
CAPACITY	4000	3880	3760	3560	3290	3020	2750

STANDARD FEATURES

MODEL NUMBER: LMS-EBT-46-4 CAPACITY: 4,000 LBS

LOST LOAD - 270 LBS

OVERALL HEIGHT - 13 1/2" LENGTH (RETRACTED) - 55 1/4"

LENGTH (EXTENDED) - 93"

OVERALL WIDTH - 32"

USABLE FORK POCKET - 2 1/2" X 7 1/2" 24" FORK POCKET CENTERS

31" MINIMUM HOOK POINT 90 3/8" MAXIMUM HOOK POINT

EFFECTIVE THICKNESS: LESS THAN 1"

NEVER EXCEED LOAD CENTER RATING PER FORK TRUCK MANUFACTURER'S GUIDELINES DO NOT USE THIS FORK TRUCK ATTACHEMENT IF LOAD WILL EXCEED FORK TRUCK MANUFACTURER'S LOAD CENTER RATING.

SPECIAL FEATURES NONE

Ρ P R 0 V Α

AND LOCAL REGULATIONS AND STANDARDS. ANY MODIFIED UNITS ARE NON-RETURNABLE [] As drawn [] As marked

Χ

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS

REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO

CONFIRM PRODUCT AND INSTALLATION

COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE

DIMENSION TOLERANCE ± 1/4"

Signed: Printed Name:

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

DISTRIBUTOR'S NAME:

VESTIL MANUFACTURING

W.O.# X

SALES

ENG.

POWER

FAB.

FOR INTERNAL USE ONLY

PROJECT SIGN OFF

DRAWN BY: BCN DATE: 8/22/2016

SALES: X

Date:

REFERENCE: X SCALE: 1:22 FILE NAME: QUOTED LEAD TIME: X QUOTE # 08-007-210