CUSTOMER INFORMATION	HDD DRUM DUMPER
CONTACT:	
COMPANY:	SURVEY SHEET
PHONE:	
EMAIL:	
CONTAINER TYPE & SIZE	
HDD WORKS WITH STANDARD 55- AND 30-GALLON PLASTIC, STEEL, AND FIBER DRUMS. IF YOU WOULD LIKE TO DUMP A DIFFERENT CONTAINER, PLEASE SPECIFY SIZE:	ROTATED
LENGTH: WIDTH:	45° DUMP
HEIGHT: DIAMETER:	ANGLE
IF YOU PLAN TO USE A DOLLY WITH YOUR DRUMS, PLEASE SPECIFY OVERALL SIZE OF DOLLY:	
LENGTH: WIDTH:	
HEIGHT: DIAMETER:	
STANDARD FEATURES	
DESCRIPTION (CIRCLE ONE): PORTABLE STATIONARY	LEVEL LEVEL
DUMP HEIGHT (CIRCLE ONE): 36" 48" 60" 72"	height
CAPACITY (CIRCLE ONE): 750 LBS. 1,000 LBS. 1,500 LBS	DUMP H
OPTIONS (LIST ALL THAT APPLY)	HEIGHT 1 40"
SPECIAL CHUTE REACH (STD. 14")	26" L
SPECIAL DUMP HEIGHT:	
SPECIAL CAPACITY:	<u> </u>
SPECIAL HOLD DOWN FINGER HEIGHT:	FRAME LENGTH
SPECIAL COLOR:	VESTIL
STAINLESS STEEL CHUTE***:	MANUFACTURING 2999 N. WAYNE ST.
FDA WHITE POWDER COAT FRAME:	ANGOLA, IN 46703
"STEEL IT" PAINT FRAME:	Ph: 260-665-7586 www.vestil.com
5-GALLON PAIL ADAPTOR FINGERS:	Fax: 260-665-1339 info@vestil.com
*** 304 SS MILL FINISH STANDARD. PLEASE SPECIFY IF A DIFFERENT FINISH IS REQUIRED.	Is this a repeat quote or repeat order? If yes, please idicate
POWER (150V, 1 PHASE STANDARD) IF CUSTOM, INDICATE BELOW	Prev. Quote No.: Prev. Order No.:
A/C: 110V 220V 460V OTHER	SINGLE PHASE THREE PHASE
12V D/C (115V ON-BOARD BATTERY CHARGER INCLUDED)	
ROTARY AIR / HYDRAULIC (80 CFM @ 80 PSI, 1/2 GPM)	RECIPROCATING AIR / HYDRAULIC (15 CFM @ 100 PSI, 1/4 GPM)
CONTROLS: HAND FOOT AUTOMATED	
POWER UNIT: EXTERNAL INTERNAL (STANDARD)	
IF EXTERNAL, LENGTH OF CORDS (8' STD):	
IF ANY OTHER SPECIAL POWER OR CONTROLS ARE REQUIRED, PLEASE INDICATE:	
CONTROLS ARE REQUIRED, PLEASE INDICATE.	
APPLICATION INFORMATION	
DUTY CYCLE: STARTS PER HOUR: HOURS F	PER SHIFT
SHIFTS PER DAY: DAYS P	
DUTY CYCLE IS CALCULATED BY STARTS PER HOUR OR NUMBER OF TIMES "UP" BU	
ANTICIPATED CYCLE TIME:	
SPECIAL TEMPERATURE REQUIREMENTS:	
ARE THERE OVERHEAD HEIGHT RESTRICTIONS?	
IS THIS A HAZARDOUS LOCATION? IF YES: CLASS:	DIV: GROUP:
OTHER SPECIAL REQUESTS OR APPLICATION INFORMATION:	