

HL 10000 Pedestal Desks

Desk Widths	Single Pedestal - 48", 66" Double Pedestal - 60" Return desk - 42"
Desk Height	29.5"
Desk Depth	Single Pedestal - 30" Double Pedestal - 30" Return desk - 24"
Lock	Central lock system for single & double pedestal desks Returns are non locking
Interlock	Not available
Legs	Include 1 leveling glide per leg
Tops	Thermal fused melamine with 1.125" thick particleboard core Edgebanding - .5mm
Divider (optional)	4.25"H x 11.75"W

DRAWERS

	Cabinet Size	Inside Drawer Dimension			Load Capacity per drawer (lbs)
		H	W	D	
File Drawer	Return desk	11.01"	11.98"	17.00	38.1
	Single & double ped desk	11.01"	11.98"	20.00	44.8
Box Drawer	Return desk	5.07"	11.98"	17.00	26.8
	Single & double ped desk	5.07"	11.98"	20.00	31.6
Center Drawer	Single ped desk	2.45"	17.95"	16.31	12.2
	Double ped desk	2.45"	23.95"	16.31	16.3

TOP LOAD

Desk Top Load Capacity

Our cabinets pass both the concentrated and functional distributed load tests.

The Concentrated load is 200 lbs

The Functional Distributed load is 324 lbs. evenly distributed on the top.