




Powered by Menasha Corporation

## PRODUCT APPLICATION SHEET

# KD3230-25

The medium-duty BulkPak® 3230 KD Series reusable containers are ideal for high density small to medium sized parts and are perfect for tight working spaces.



Containers collapse when empty for reduced return transportation costs and warehouse space savings. During storage and shipping these bulk bins stack securely atop each other. Large, spring-loaded ergonomic latches make collapsing containers and opening/closing access doors extremely easy. Designed to hold 1,500 lbs, these collapsible containers are built for medium-duty applications. Palletboxes offer the strength and rugged durability demanded in today's material handling and distribution systems. Custom protective dunnage is available for all ORBIS BulkPak containers. These plastic containers are fully recyclable at the end of their service life. (All dimensions and specifications are approximate. Performance characteristics are based on uniform static loads and may be affected distribution of load, handling methods, number and type of access doors and temperatures beyond the range of 0 to 120 degrees Fahrenheit.)

### BENEFITS

- 32" x 30" x 25" footprint
- Structural-foam molded in high-density polyethylene
- Container capacity: 1,500 lbs
- Access doors: 0
- 1 or 2 doors on the 32" side (Door configurations vary by model)
- Deck: Closed
- Base: All-plastic picture frame bottom
- Non-sequential wall hinge design allows palletbox sidewalls to completely collapse to prevent wall and hinge damage

- Popular applications: Automotive components, bearings, hardware, industrial equipment, metal parts, plastics and rubber parts, resin and powder and tools



Powered by Menasha Corporation

## PRODUCT APPLICATION SHEET

KD3230-25

Outside Top Dimensions Length	32.0"
Outside Top Dimensions Width	30.0"
Outside Top Dimensions Height	25.0"
Inside Top Dimensions Length	29.2"
Inside Top Dimensions Width	27.3"
Product Clearance	18.1"
Collapsed Height	13.1"
Container Capacity	1,500 lbs
Weight	68 lbs
Internal Volume	8.4 ft <sup>3</sup>
Maximum Loaded Stack Static	6 high
Maximum Loaded Stack Dynamic	4 high
Return Ratio	2.3:1
Access Door Openings Height Long Side	10.5"
Access Door Openings Width Long Side	18.0"
Fork Openings Height Long Side	3.5"
Fork Openings Height Short Side	4.2"
Fork Openings Width Long Side	11.1"
Fork Openings Width Short Side	7.3"
40 Ft Container Quantities Without Covers Collapsed	294
40 Ft Container Quantities Without Covers Assembled	168
Truckload Quantities 53 Ft Without Covers Collapsed	480
Truckload Quantities 53 Ft Without Covers Assembled	240