




MEMBER OF TROAX® GROUP

Providing Reliable Engineered Solutions


## Stor-More® Dispatcher Employee Locker Installation Instructions

### TABLE OF CONTENTS:

PAGE 1	COVER, TOOLS REQ'D
PAGE 2	SPECIFICATIONS
PAGE 3	HARDWARE PROVIDED
PAGE 4	PARTS LIST
PAGE 5	ASSEMBLY INSTRUCTIONS
PAGE 6	ASSEMBLY INSTRUCTIONS (CONTINUED)




### TOOLS REQUIRED:




7/16"  
[11mm]

OPEN END WRENCH



MEASURING TAPE



LEVEL

D

1

24

24

0

**FRONT**

1 - SINGLE TIER FRONT DOOR  
2 - DOUBLE TIER FRONT DOOR  
3 - TRIPLE TIER FRONT DOOR

**WIDTH**


24 - 24" WIDE  
30 - 30" WIDE  
36 - 36" WIDE

**DEPTH**


24 - 24" DEEP  
30 - 30" DEEP  
36 - 36" DEEP

**REAR**

0 - WELDED WIRE MESH  
1 - SINGLE TIER REAR DOOR  
2 - DOUBLE TIER REAR DOOR  
3 - TRIPLE TIER REAR DOOR



SINGLE TIER



DOUBLE TIER

PART NO.	WIDTH	DEPTH	HEIGHT	PART NO.	WIDTH	DEPTH	HEIGHT
D1-2424-0		24"		D2-2430-1		31.5"	
D1-2424-1		25.5"		D2-2430-2		31.5"	
D1-2424-2		25.5"		D3-2430-0		30"	
D1-2424-3		25.5"		D3-2430-1		31.5"	
D2-2424-0		24"		D3-2430-3		31.5"	
D2-2424-1		25.5"		D1-2436-0		36"	
D2-2424-2		25.5"		D1-2436-1		37.5"	
D3-2424-0	24"	24"	79.5"	D1-2436-2	24"	37.5"	79.5"
D3-2424-1		25.5"		D1-2436-3		37.5"	
D3-2424-3		25.5"		D2-2436-0		36"	
D1-2430-0		30"		D2-2436-1		37.5"	
D1-2430-1		31.5"		D2-2436-2		37.5"	
D1-2430-2		31.5"		D3-2436-0		36"	
D1-2430-3		31.5"		D3-2436-1		37.5"	
D2-2430-0		30"		D3-2436-3		37.5"	
PART NO.	WIDTH	DEPTH	HEIGHT	PART NO.	WIDTH	DEPTH	HEIGHT
D1-3024-0		24"		D2-3030-1		31.5"	
D1-3024-1		25.5"		D2-3030-2		31.5"	
D1-3024-2		25.5"		D3-3030-0		30"	
D1-3024-3		25.5"		D3-3030-1		31.5"	
D2-3024-0		24"		D3-3030-3		31.5"	
D2-3024-1		25.5"		D1-3036-0		36"	
D2-3024-2		25.5"		D1-3036-1		37.5"	
D3-3024-0	30"	24"	79.5"	D1-3036-2	30"	37.5"	79.5"
D3-3024-1		25.5"		D1-3036-3		37.5"	
D3-3024-3		25.5"		D2-3036-0		36"	
D1-3030-0		30"		D2-3036-1		37.5"	
D1-3030-1		31.5"		D2-3036-2		37.5"	
D1-3030-2		31.5"		D3-3036-0		36"	
D1-3030-3		31.5"		D3-3036-1		37.5"	
D2-3030-0		30"		D3-3036-3		37.5"	

DEPTH GROWS BY 1.5" WHEN A REAR ACCESS DOOR IS INSTALLED


D 1 24 24 0

**FRONT**  
 1 - SINGLE TIER FRONT DOOR  
 2 - DOUBLE TIER FRONT DOOR  
 3 - TRIPLE TIER FRONT DOOR

**WIDTH**  
 24 - 24" WIDE  
 30 - 30" WIDE  
 36 - 36" WIDE

**DEPTH**  
 24 - 24" DEEP  
 30 - 30" DEEP  
 36 - 36" DEEP

**REAR**  
 0 - WELDED WIRE MESH  
 1 - SINGLE TIER REAR DOOR  
 2 - DOUBLE TIER REAR DOOR  
 3 - TRIPLE TIER REAR DOOR




TRIPLE TIER

PART NO.	WIDTH	DEPTH	HEIGHT	PART NO.	WIDTH	DEPTH	HEIGHT
D1-3624-0		24"		D2-3030-1		31.5"	
D1-3624-1		25.5"		D2-3030-2		31.5"	
D1-3624-2		25.5"		D3-3030-0		30"	
D1-3624-3		25.5"		D3-3030-1		31.5"	
D2-3624-0		24"		D3-3030-3		31.5"	
D2-3624-1		25.5"		D1-3036-0		36"	
D2-3624-2		25.5"		D1-3036-1		37.5"	
D3-3624-0	36"	24"	79.5"	D1-3036-2	36	37.5"	79.5"
D3-3624-1		25.5"		D1-3036-3		37.5"	
D3-3624-3		25.5"		D2-3036-0		36"	
D1-3030-0		30"		D2-3036-1		37.5"	
D1-3030-1		31.5"		D2-3036-2		37.5"	
D1-3030-2		31.5"		D3-3036-0		36"	
D1-3030-3		31.5"		D3-3036-1		37.5"	
D2-3030-0		30"		D3-3036-3		37.5"	

DEPTH GROWS BY 1.5" WHEN A REAR ACCESS DOOR IS INSTALLED

**HARDWARE PROVIDED:**




**HARDWARE LIST**


- (K) 1/4"-20 FLANGE NUT
- (D) 1/4"-20 x 1/2" SQUARE NECK CARRIAGE BOLT

**PARTS LIST:**


FRONT:  
FRAMED DOORS



SINGLE TIER  
x1




DOUBLE TIER  
x1




TRIPLE TIER  
x1

SIDES:  
FRAMED PANELS




DOUBLE TIER  
x2




SINGLE &  
TRIPLE TIER  
x2

TOP & BOTTOM:  
SHEET METAL



x2


HARDWARE KIT:




x1

**OPTIONS:**


REAR:  
FRAMED DOORS




MESH BACK  
x1



SINGLE TIER  
x1




DOUBLE TIER  
x1



TRIPLE TIER  
x1

SHELVES:  
SHEET METAL SHELF




x0 = SINGLE TIER LOCKER  
x1 = DOUBLE TIER LOCKER  
x2 = TRIPLE TIER LOCKER


# 1

# 2

**NOTE:** REPEAT STEP 1 FOR EACH SHELF. REFER TO PARTS LISTS FOR NUMBER OF SHELVES PER LOCKER.




**NOTE:** USE (x6) OF (K) & (D) FOR 36" DEEP LOCKERS




**NOTE:** DO **NOT** TIGHTEN ANY NUTS, FULLY TIGHTEN AFTER LAST STEP


# 3



# 4



# 5



**NOTE:** MEASURE AND LEVEL THE LOCKER, THEN TIGHTEN ALL NUTS