



The all-in-one solution in protective eyewear, Genesis XC eyewear sets the standard for extra coverage and extra comfort on the job. Its design extends protection and offers more than 180 degrees of peripheral coverage. Additionally, its ergonomically balanced MMT — Multi-Material Technology® frame provides exceptional all-day comfort. With the Rx lens insert, it offers an alternative for workers requiring vision correction. It holds Rx lenses snugly inside the comfortable Genesis XC eyewear, shielding expensive prescription lenses from damage. The Genesis XC provides all-day comfort and coverage, and especially for prescription lens wearers, nothing protects like Genesis XC with the Rx lens insert.



SAFETY EYEWEAR

Genesis XC™

UVE[®]X™
by SPERIAN



Genesis XC™

High Performance Protection

- Extended wrap-around lens for extra cheek and extra side coverage (up to 20% more than the standard Genesis® lens)
- Available with Dura-streme™ dual coating technology which combines our two best lens coatings — Uvextreme® anti-fog on the interior and Ultra-dura® anti-scratch on the exterior — for 3x longer lens life*
- Offers highest available impact protection. Meets ANSI Z87.1-2003 (High Impact) and military V₀ ballistic impact test (protection against impact energies 7x higher than ANSI requirements)
- Certified to meet CSA Z94.3 standards
- Available in a wide range of lens tints to address the needs of a variety of work environments

Superior Comfort & Fit

- Soft elastomer browguard diffuses and deflects impact while providing comfort at all contact points

- Soft flexible fingers on the nose piece adjust and conform to almost any nasal profile to reduce slippage
- Adjustable, ratcheting temples allow customized lens inclination and fit
- Cushioned temple tips offer all-day comfort

Product Platform Advantages

- Economical and easy lens replacement system allows for multiple lens tints and extends the life of the eyewear
- Optional Rx lens insert holds prescription lenses securely, and accommodates a variety of Rx needs, including bifocals, trifocals and progressive lenses. With a classic screw closure, it easily fits prescriptions ranging from +3.0 to -3.0 D and offers an economical option for workers who require vision correction
- Multiple models in a family offers standardization while offering workers choice
- Lifetime frame guarantee



Ratcheting temples permit the lenses to be tilted away from the cheeks and allow wearer to modify the angle, ensuring customized fit and comfort.



Soft, flexible nose fingers conform to fit a variety of nasal profiles.



Cushioned temples for non-slip fit and all-day comfort. Adjustable temple length allows individual worker customization for added comfort.



Extended 9-base wrap-around lens provides up to 20% more coverage around the eyes and cheeks than the standard Genesis® lens.



*Comparative lens life test performed using a Bayer Abrasion Test method and may vary between environment and application.

Genesis XC™



All Uvex® lenses offer 99.9% ultra-violet protection.



Clear — Used for most indoor work applications



Gray — Minimizes eye fatigue due to outdoor sunlight and glare



Amber — For low-light applications where enhanced contrast is needed



Silver Mirror — Deflects sunlight and glare



SCT-Vermilion — For indoor applications where contrast is needed, such as inspection



SCT-Blue — For applications with high levels of sodium vapor lighting



SCT-Reflect 50 — Light mirror coating for varying light conditions



SCT Gray — Minimizes outdoor glare and offers true color recognition



SCT-Low IR — When peripheral IR protection is required



Infra-dura® Welding — Available in shades 2.0, 3.0 and 5.0 for welding, brazing and cutting

ORDERING INFORMATION

EYEWEAR

ITEM #	FRAME COLOR	LENS TINT	LENS COATING	UPC CODE
S3300	Black	Clear	Ultra-dura	603390113826
S3300-ADV	Black w/Advanced TPE	Clear	Ultra-dura	603390123412
S3300D	Black	Clear	Dura-streme	603390122866
S3300X	Black	Clear	Uvextreme	603390113833
S3300X-ADV	Black w/Advanced TPE	Clear	Uvextreme	603390122972
S3301	Black	Gray	Ultra-dura	603390113840
S3301X	Black	Gray	Uvextreme	603390113857
S3302	Black	SCT-Reflect 50	Ultra-dura	603390113864
S3303X	Black	SCT-Gray	Uvextreme	603390113871
S3304X	Black	SCT-Low IR	Uvextreme	603390113888
S3305	Black	Shade 2.0 Infra-dura	Ultra-dura	603390113895
S3306	Black	Shade 3.0 Infra-dura	Ultra-dura	603390113901
S3307	Black	Shade 5.0 Infra-dura	Ultra-dura	603390113918
S3308	Black	Silver Mirror	Ultra-dura	603390113970
S3309	Black	Amber	Ultra-dura	603390114991
S3310X	Black	50% Gray	Uvextreme	603390116124
S3311X	Black	SCT-Vermilion	Uvextreme	603390116803
S3312X	Black	SCT-Blue	Uvextreme	603390116810

REPLACEMENT LENSES

ITEM #	LENS TINT	LENS COATING	UPC CODE
S6950	Clear	Ultra-dura	603390113987
6950D	Clear	Dura-streme	603390122934
S6950X	Clear	Uvextreme	603390113994
S6951	Gray	Ultra-dura	603390114007
S6951X	Gray	Uvextreme	603390114014
S6952	SCT-Reflect 50	Ultra-dura	603390114021
S6953X	SCT-Gray	Uvextreme	603390114038
S6954X	SCT-Low IR	Uvextreme	603390114045
S6955	Shade 2.0	Ultra-dura	603390114052
S6956	Shade 3.0	Ultra-dura	603390114069
S6957	Shade 5.0	Ultra-dura	603390114076
S6958	Mirror	Ultra-dura	603390114083
S6959	Amber	Ultra-dura	603390115004
S6960X	50% Gray	Uvextreme	603390116131
S6961X	SCT-Vermilion	Uvextreme	603390116827
S6962X	SCT-Blue	Uvextreme	603390116834

RX INSERT

ITEM #	DESCRIPTION	UPC CODE
S3350	Genesis XC Rx Insert	603390114885
S3351	Pattern for Rx Insert	603390117299

Packaging Information (Eyewear):
Ind. Box, 10/Stock, 200/Master Case
Master Case Weight: 33 pounds
Master Case Dimensions: 29" x 15" x 24"

Packaging Information (Rx Insert):
Ind. Box, 10/Stock, 200/Master Case

Packaging Information (Replacement Lenses):
Ind. Polybag, 10/Box, 200/Master Case
Master Case Weight: 11 pounds
Master Case Dimensions: 18" x 13 1/4" x 10"

Uvextreme® anti-fog coating performs under the most extreme conditions and will not wear off after repeated cleanings. It is permanently bonded to the lens and retains anti-scratch, anti-static and UV protection properties. Ultra-dura® hard coat is permanently bonded to the lens and is scratch-resistant and chemical-resistant. Uvex Dura-streme™ lenses combine our two best lens coatings on one lens: Ultra-dura on the exterior and Uvextreme on the interior to provide up to 3x more lens life. Advanced TPE formulation performs exceptionally well in environments where chemical mist, cutting oils and high moisture are present.



FOR MORE INFORMATION, CONTACT:

Sperian Protection Americas, Inc.
900 Douglas Pike
Smithfield, RI 02917-1874
(800) 430-5490
www.uvex.us

UVEX
by SPERIAN