

BR 18/1 MW

Multi-Purpose Scrubber

Low-Moisture for Hard and Soft Floors

BR 18/1 MW



Model# 99418



The BR 18/1MW scrubber is easier on the indoor environment and makes cleaning so quiet and simple it is actually enjoyable. In-house facility managers, building engineers, housekeepers and BSCs will appreciate the BR 18/1 Scrubber's superior flexibility, advanced productivity and reduced environmental impact. Where high quality floor cleaning performance, ease of use and durability are called for, the BR 18/1 is the most versatile and effective answer for any hard or soft floor surface.

PRODUCT SPECIFICATIONS	
Model	BR 18/1 MW
Catalog Number	99418
MACHINE DIMENSIONS	
Dimensions (L X W X H)	15" x 21" x 44"
Net Weight	44 Lbs.
Solution / Recovery Tank	1 gal / .3 gal.
DESIGN CHARACTERISTICS	
Tank construction	Polyethylene
Brush Type	2, counter-rotating cylindrical
Brush Width	16.5 in
Brush RPM	650 rpm
Cleaning Path	18 in
Cleaning Rate	3,772 sq. ft./hr.
Sound Level	69 db (A)
Cord Length	40 ft.
Brush Motor	1000 W
REPLACEMENT ITEMS	
Standard Brush	33985
Soft Brush	33986
Hard Brush	33987
Escalator Brush	33988
Carpet Brush	33989
Side Brush	33991
Transport Trolley	05-3395-0500




TRANSPORT EASILY

For fast and simple transport, an optional trolley is available.



COMPACT

The BR 9/1 MW takes automatic scrubbing into confined, small-areas where bigger units can not go.




REMOVABLE RECOVERY TANK

Provides easy access and cleanup



SOLUTION ATOMIZATION CLEANING SOLUTION

is atomized into a fine mist and dispersed through the cylindrical brushes, so less moisture is consumed during the hard floor or carpet cleaning process.



OPTIONAL SIDE BRUSH

provides superior edge-cleaning capability and widen your cleaning path even further, delivering access to tight corners and hard-to-reach spaces.