

## Swivel/Tilt Wall Mount for 13" to 27" TVs and Monitors

MODEL NUMBER: DWM1327SE



Hangs a flat-panel television, monitor or other display on the wall. Ideal for home, office, hotels, bars and restaurants. Swivels and tilts to provide optimal viewing angles.

### Description

The VESA-compliant DWM1327SE Swivel/Tilt Wall Mount allows you to mount your flat-panel television, monitor or other display on the wall. Ideal for home, office, hotels, bars and restaurants, it fits most flat-panel displays from 13 to 27 inches.

The full-motion swivel arm can be adjusted for angle to give you maximum flexibility in positioning your display to fit your environment and comfort level. A 180° swivel and -15° to +15° tilt capability minimizes glare and provides comfortable viewing from multiple angles.

Durable all-metal frame with scratch-resistant powder-coated finish supports up to 33 pounds. Comes fully assembled for quick mounting to the wall with included hardware. Conforms to VESA-compliant displays with any of the following mounting hole patterns: 75 x 75 mm and 100 x 100 mm.

### Features

#### Mounts Your TV or Monitor to the Wall

- Fits most flat-panel televisions, monitors and other displays from 13 to 27 in.
- Ideal for home, office, hotels, bars and restaurants
- Full-motion swivel arm adjusts for angle
- Mounting hardware included

#### Convenient One-Touch Adjustment

- 180° swivel and -15° to +15° tilt capability provides comfortable viewing from multiple angles

#### Durable Metal Construction

### Highlights

- Fits most flat-panel displays from 13 to 27 in.
- One-touch adjustment for comfortable viewing
- 180° swivel and -15° to +15° tilt for wide range of motion
- Supports up to 33 lb.

### Package Includes

- DWM1327SE Swivel/Tilt Wall Mount for 13" to 27" TVs and Monitors
- (4) M4 screws
- (4) M5 screws
- (4) Anchor bolts
- (4) Concrete anchors
- Hex key, 4 mm
- Hex key, 5 mm
- Owner's manual



- Supports up to 33 lb.
- Scratch-resistant powder-coated finish blends with any décor
- Fully assembled for immediate installation

#### VESA Compliance

- Supports the following VESA mounting hole patterns: 75 x 75 mm and 100 x 100 mm

## Specifications

OVERVIEW	
UPC Code	037332183514
PHYSICAL	
Mounting Location	Wall
Shipping Dimensions (hwd / in.)	9.40 x 2.80 x 11.00
Shipping Dimensions (hwd / cm)	23.88 x 7.11 x 27.94
Shipping Weight (lbs.)	2.50
Shipping Weight (kg)	1.13
Unit Dimensions (hwd / in.)	8.27 x 15.94 x 4.6
Unit Dimensions (hwd / cm)	21.0 x 40.49 x 11.7
Unit Weight (lbs.)	2.66
Unit Weight (kg)	1.21
Material of Construction	Steel
Color	Black
VESA Pattern (mm)	75x75; 100x100
Motion	Full
Degrees of Motion	-15/+15 Tilt; 180 Swivel
Min/Max Arm Extension (in.)	4.14 min to 15.95 max
Min/Max Arm Extension (cm)	10.5 min to 40 max
Maximum Weight Capacity (lbs.)	33
Maximum Weight Capacity (kg)	15
Minimum Screen Size (in.)	13
Maximum Screen Size (in.)	27
Minimum Screen Size (cm)	33.02
Maximum Screen Size (cm)	68.58
Number of Displays	1



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<b>FEATURES &amp; SPECIFICATIONS</b>	
Tools Necessary	Yes
Cord Management	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>