

MLRS8MCLK



50" x 23.38" x 24.38" (H x W x D)

All-refrigerator for breast milk storage with 4 lockers with combination locks.

Highlights:

Perfect for employee wellness rooms, daycare centers, and lactation lounges

Ideal for work environments and offices complying with Section 4207 of the Patient Protection and Affordable Care Act

Preset temperature range as recommended by the CDC for mother's milk storage

Product Features:

Easy to use	User-friendly design ensures effortless use for mothers and facility managers alike
Lockers	Four lockers sized at 11" H x 9 3/8" W x 15 1/4" D can hold regular and large-size maternity bags and accessories
Individual access	Combination locks provide separate access and privacy for nursing mothers
CDC-compliant temperature	Preset temperature remains within recommended range for mother's milk storage
Hospital-grade construction	Ensures safe and compliant storage with 2-year parts and labor / 5-year compressor extended warranty
Locker key	Overrides combination locks to access locker contents as necessary
Door lock	Added security on the exterior door (2 keys included)
Reversible door	Provides flexibility in product placement
LED display	Allows for easy reading of unit temperature

MLRS8MCLK Specifications:

Overview	
Height of Cabinet	50.0" (127 cm)
Width	23.38" (59 cm)
Width with Door Open	23.88" (61 cm)
Depth	24.38" (62 cm)
Depth with Handle	23.13" (59 cm)
Depth with door at 90°	46.5" (118 cm)
Capacity	8.0 cu.ft. (227 L)
Defrost Type	Automatic
Door	White
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Amps	1.4
Voltage/Frequency	115 V AC/60 Hz
Weight	180.0 lbs. (82 kg)
Shipping Weight	190.0 lbs. (86 kg)
Estimated Time to Ship	5 to 7 days
Parts & Labor Warranty	2 Years
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Shelf Type	Lockers
Thermostat Type	Digital
Fan Type	Interior
Refrigerant Type	R600a
Refrigerant Amount	1.73oz.
Interior Light	Yes
Temperature Range	33 to 40°F
Dimensions	
Interior Height	41.25" (105 cm)
Interior Width	20.0" (51 cm)
Interior Depth	17.0" (43 cm)
Compressor Step Height	5.5" (14 cm)
Compressor Step Width	20.0" (51 cm)
Compressor Step Depth	5.0" (13 cm)

