

# MLRS1MC



21.5" x 17.5" x 19.75" (H x W x D)

All-refrigerator for breast milk storage with 2 adjustable shelves

## Highlights:

Ideal for work environments and offices complying with Section 4207 of the Patient Protection and Affordable Care Act

Perfect for employee wellness rooms, daycare centers, and lactation lounges

Preset temperature range as recommended by the CDC for mother's milk storage

## Product Features:

Easy to use	User-friendly design ensures effortless use for mothers and facility managers alike
CDC-compliant temperature	Preset temperature remains within recommended range for mother's milk storage
Adjustable wire shelves	Multiple shelf positions spaced at 1/2" for improved air circulation and storage
Countertop design	Sized perfectly for countertop use
Sealed cabinet design	Allows for unit to be freestanding
Door lock	Added security on the exterior door (2 keys included)
Reversible door	Provides flexibility in product placement
LED display	Allows for easy reading of unit temperature
Power loss alarm	Alerts when unit loses power; NOTE: Alarm is battery-powered and has a limited time to alarm

## MLRS1MC Specifications:

Overview	
Height of Cabinet	21.5" (55 cm)
Width	17.5" (44 cm)
Width with Door Open	18.0" (46 cm)
Depth	19.75" (50 cm)
Depth with Handle	21.5" (55 cm)
Depth with door at 90°	36.0" (91 cm)
Capacity	1.0 cu.ft. (28 L)
Defrost Type	Automatic
Door	White
Cabinet	White
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Amps	0.6
Voltage/Frequency	115 V AC/60 Hz
Weight	60.0 lbs. (27 kg)
Shipping Weight	70.0 lbs. (32 kg)
Estimated Time to Ship	3 to 5 days
Parts & Labor Warranty	2 Years
Compressor Warranty	5 Years
Refrigerator Features	
Door Swing	RHD
Reversible	Yes
Shelf Type	Wire
Shelf Qty	3
Adjustable Shelves	Yes
Thermostat Type	Digital
Fan Type	Interior
Refrigerant Type	R600a
Refrigerant Amount	0.71oz.
Interior Light	Yes
Temperature Range	33 to 40°F
Dimensions	
Interior Height	15.75" (40 cm)
Interior Width	14.0" (36 cm)
Interior Depth	8.0" (20 cm)

