



products meet or exceed applicable ANSI/BIFMA standards




SPECS:

- Available in 3 rectangular sizes – 60", 72", 96"
- 1 3/4" thick top for the BT3060 & BT3072
- 2" thick top for the BT3096
- Lightly spotted grey top w/ grey textured powder coated wishbone shaped legs
- 17-gauge strength frame; 18-gauge legs
- 1,000lb. weight capacity on BT3060 & BT3072
- 800lb. weight capacity on BT3096
- Stack up to 12 high on DY3072 or DY3096
- Can withstand heat up to 212 degrees Fahrenheit
- Gravity slide lock for extra stability
- Lightly textured surface to resist scratching yet smooth enough to write on
- UV Protected for outdoor use

MODEL BT3072 SHOWN

Tables can withstand heat up to 212°F!





NEATLY FOLDED UNDERSIDE SHOWING LEGS, CROSSBARS & STEEL CHANNELS



MODEL BT3072-20 SHOWN





BT3072



BT3096



BT3060



PLASTIC / FRAME COMBINATIONS

BT3000 SERIES
SPECKLED GREY PLASTIC / GREY TEXTURED FRAME

BT3072-20 SERIES
CHARCOAL SLATE PLASTIC / SILVER FRAME

USE WITH:

Model DY3072/3096
Folding Table Dolly

CAPACITY: STACKS UP TO 12 TABLES HIGH



Model DYMU
Folding Table Dolly

FOR USE WITH ROUND AND/OR RECTANGULAR TABLES



National Public Seating

