

ToGo

MOBILE BOOTH SYSTEM



BOOTH SYSTEM FOR EASY COLLABORATION.

PRIMARY FEATURES




BOOTH SEATING

The ToGo benches feature fixed high backs with a slight 12-degree pitch providing the perfect contour for comfortable seating.



COLLABORATIVE

Today's cafeterias have become multi-purpose spaces which require furniture that is mobile and multi-functional. NPS's ToGo Booth System is ideal for such an environment.



MOBILE

Built with 14 gauge steel, 2" tube legs, and double ball bearing non-marring 3" casters, the ToGo provides the ultimate in strength and mobility.



ADDITIONAL FEATURES

EASE OF USE

It's simple to reconfigure for multi-purpose use. With its Heavy-duty 3" casters the ToGo Booth is easy to move. Rubber Grip-Tight glides automatically engage with the floor when opened along with locking casters to keep your seating arrangement nicely in place. Tables open and lock automatically and are easily released with a pull of a handle.



LATCH




GRIP-RITE GLIDE



HEAVY-DUTY 3" CASTERS


SIMPLE STORAGE

The ToGo Bench and Table top flip up and nest for optimal storage. Both are offered in 48" or 60" widths and 24" or 30" depths providing comfortable seating for all sizes.



15"H

12"W



19"H

15"W

MORE seating comfort than a Convertible Bench!



TOGO TABLE

Model	Seats	Open Footprint	Folded Footprint	Weight
TGT2448	2-3	24"W x 48"L x 29"H	21.25"W x 48"L x 39.50"H	58 lbs.
TGT2460	3-4	24"W x 60"L x 29"H	21.25"W x 60"L x 39.50"H	64 lbs.
TGT3048	2-3	30"W x 48"L x 29"H	21.25"W x 48"L x 39.50"H	68 lbs.
TGT3060	3-4	30"W x 60"L x 29"H	21.25"W x 60"L x 39.50"H	76 lbs.



TOGO BENCH

Model	Seats	Open Footprint	Folded Footprint	Weight
TGB48	2-3	25"W x 48"L x 38"H	17.25"W x 48"L x 38"H	74 lbs.
TGB60	3-4	25"W x 60"L x 38"H	17.25"W x 60"L x 38"H	86 lbs.
TGB48	2-3	25"W x 48"L x 38"H	17.25"W x 48"L x 38"H	72 lbs.
TGB60	3-4	25"W x 60"L x 38"H	17.25"W x 60"L x 38"H	84 lbs.



TOGO BOOTH SET

Model	Seats	Open Footprint	Folded Footprint	Weight
TGBTH2448	4-6	74"W x 48"L	34.5"W x 48"L x 39.5"H	206 lbs.
TGBTH2460	6-8	74"W x 60"L	34.5"W x 60"L x 39.5"H	236 lbs.
TGBTH3048	4-6	80"W x 48"L	34.5"W x 48"L x 39.5"H	216 lbs.
TGBTH3060	6-8	80"W x 60"L	34.5"W x 60"L x 39.5"H	248 lbs.

STANDARD LEAD TIME IS 6 WEEKS





QUICK SHIP

10 DAY QUICKSHIP OPTION
Model #TGBTH2460PEMDGYNLNL

Table Color: Grey Nebula **Bench Back/Seat Color:** Navy Legacy

TABLE & BENCH CORE OPTIONS



MDF (MD)




Particleboard (PB)



Plywood (PW)


FRAME COLOR



Powder Coated (PC)



STANDARD LAMINATE OPTIONS



Grey Nebula (GY)



Montana Walnut (WT)



Banister Oak (OK)



Wild Cherry (CH)



Fusion Maple (FM)



Marigold (YW)



Hollyberry (RE)



Persian Blue (BL)

CUSTOM LAMINATE OPTIONS

More Wilsonart laminate options available!




Asian Sand (7952K-18)




Antique Topaz (4863K-07)



Rustic Slate (4888-38)



Bottle Glass (4901K-01)



Ebony Star (4552K-07)




Mission Glaze (4854-38)



Berry Fizz (4935-38)



Antique Brush (4823-60)



Mystique Marine (4759-60)



Skyline Walnut (7964K-12)



Blue Agave (4919-60)



Island (D498K-18)

TABLE EDGE & BENCH OPTIONS



Vinyl T-Molding (TM)



Protect Edge | Black (PE)



Protect Edge | Navy (PN)



Protect Edge | Green (PG)



Protect Edge | Red (PR)



Protect Edge | Purple (PP)



Protect Edge | Beige (PB)

CUSTOM TABLE EDGE & BENCH OPTIONS



HAVE FUN!
Choose a different color laminate for the top and bench



MODEL NUMBER CONFIGURATION

Model Number | Core | Edge | Frame | Laminate Table Top | Laminate Bench Back | Laminate Bench Seat

TGBTH2448-PW PE PC GY RE BL