


METAL MAN[®]

ATEC8735SGC Auto-Darkening Welding Helmet



DESCRIPTION

The Metal Man ATEC8735SGC “Techno-Skull” is a solar powered helmet that uses CR2450 replacement battery backup power. It features 4 arc sensors and an BIG viewing area of 3.78 in. x 2.09 in. Adjust your shade control from 9 to 13 or put it in Grind mode to prevent darkening while grinding. Made to fit right, the 6-point adjustable head gear allows you to make it fit your way. With ANSI and CSA approval, the Metal Man ATEC8735SGC Auto-Darkening helmet is safe, functional, and attractive to users.

METAL MAN [®]	
REPLACEMENT PARTS	
Description	Part No.
• Lens kits (5 Front Cover Lenses)	MLK85
• (5 Inside Cover Lenses)	MLK735I
• Replacement lens	MRL735
• Shade control knob	MS0735
• Retaining wire	MRW8
• Sweat band	MSB8
• Headgear	MHG8

READ INSTRUCTION MANUAL BEFORE USE

SPECIFICATIONS

Item	Specification
Viewing Area	3.78" x 2.09"
Shade Control	External - Shade 9 to 13 plus Grind
Arc Sensors	4
Sensitivity & Delay	Internal - Dial Adjustable
Darkening Speed	1/25,000 sec.
Lens Power	Solar plus replaceable CR2450 Battery
Head Gear	5-Point Adjustable
Low Amp TIG	5 Amps
Cheater Lens	Standard 2" x 4-1/4" Compatible
Warranty	2 Year Lens Replacement
Shipping Each	12" x 12" x 12" 3 lbs. UPC#858709002883
Shipping Case of 4	26" x 25" x 13" 11 lbs. UPC#10858709002880

Order Part Number: ATEC8735SGC

METAL MAN[®]