

BossLifts[™] by herkules[™]

Straight Vertical Lifting Power with

Vehicle Lifts

Selecting the Right Lift is Essential to a Shop's Success.

“Saving money” with a lift that wears out and falls apart has its costs: replacement parts, unplanned downtime, and staff unwilling or unable to use the inexpensive but unreliable lift. If you don't want vehicle lifts to have a regular place on your annual budget, **buy the lift that lasts.**

Providing a pure vertical lift, BossLifts by Herkules vehicle lifts move cars, vans and SUVs with ease and stability. The BossLifts by Herkules vehicle lift line provides support for all types of automotive-focused work: auto body repair, detailing, windshield repair, inspection, vinyl wrapping, graphic wrapping, tire rotation, brake work—any task that requires strong, dependable lifting power.

Our patented air-bag technology serves as the main lifting force for the majority of our lifts, adding years of life to the scissors. And the inflation safety valve is standard, providing protection against air bag over-inflation.

BossLifts by Herkules vehicle lifts are proudly made in the USA with American steel.



Straight, Vertical Lifting That Powers Shops to Grow




Give Techs a Raise
By bringing work to their level
with BossLifts pneumatic options.

- VLA05 - 28.75" raised height
- K900 Series - 29" raised height
- L1200 Series - 36" raised height
- VLA04 - 42" raised height



K900

VLA05



L1200

VLA04

Ergonomics are not just for manufacturing plants; investing in quality equipment that positions a vehicle at the preferred working height for each job decreases tech strain, and reduces cycle times, which means more customers can be serviced each day, in each bay.

Take a lift to where it is needed—in, or just outside—of the shop. With BossLifts portable options, shops can easily move lifting power to where it is needed.

A VEHICLE LIFT built to last makes downtime a thing of the past.




K900P

L1200P



L1200S




K900S

Suspend, even end, loading times with BossLifts K900S and L1200S drive-on/drive-off lifts, with no lifting blocks to position. The four removable loading ramps can also pivot upward and lock in place, serving as wheel chocks.




Greater Productivity and Profits



VLA03

Superior Pneumatic Dual Platform Lifts provide Powerful, Dependable and Safe Lifting for Oil and Lube Shops

When turn-around time impacts the bottom line, BossLifts dual platform lifts move vehicles with speed and confidence. The VLA03 and VLA06 feature ramps that simplify loading, and crossbars, metal height extenders and rubber blocks that support powerful and dependable lifting.



VLA06

Power Greater Profits with Improved Ergonomics

		INCREASED ANNUAL EARNINGS				
		Number of technicians				
		1	3	5	8	10
productivity Increase	1%	\$700	\$2100	\$3500	\$5600	\$7,000
	2%	\$1,400	\$4,200	\$7,000	\$11,200	\$14,000
	5%	\$3,500	\$10,500	\$17,500	\$28,000	\$35,000
	8%	\$5,600	\$16,800	\$28,000	\$44,800	\$56,000
	10%	\$7,000	\$21,000	\$35,000	\$56,000	\$70,000
	12%	\$8,400	\$25,200	\$42,000	\$67,200	\$84,000
	15%	\$10,500	\$31,500	\$52,500	\$84,000	\$105,000
	18%	\$12,600	\$37,800	\$63,000	\$100,800	\$126,000
	20%	\$14,000	\$21,000	\$35,000	\$56,000	\$140,000
	25%	\$17,500	\$52,500	\$87,500	\$140,000	\$175,000



Note: the dollar amounts are based on each tech generating \$70,000 annually.

VLA01



Hydraulic-Powered Heavy Duty Lifting

The VLH01 provides Herkules strength and reliability with hydraulic power. Lift up to eight thousand pounds by the frame with confidence, as safety stops provide additional support.

Lift over Two Tons Anywhere in the Shop with Ease

Air Jacks by BossLifts deliver 4500 lb. lift capacity and are 100% air operated)

AJ2: lowered height - 6.5 inches, raised height - 13 inches

AJ3: lowered height - 7.875 inches, raised height - 19.25 inches.

Both Air Jacks have optional extenders and adapters available. (pictured at right)



	K900	K900P	K900S	L1200	L1200P	L1200S	VLA03 (7200)	VLA04	VLA05	VLA06	VH01
Lift points	Frame	Frame	Wheels	Frame	Frame	Wheels	Frame	Frame	Frame	Frame	Frame
Capacity (lbs.)	6,000	6,000	5,000	6,000	6,000	5,000	10,000	6,000	6,000	10,000	8,000
Platform size (inches)	38 x 50	38 x 50	82 x 151	44 x 67	44 x 67	80.3 x 151	16 x 50 (2)	38.5 x 60.5	38.5 x 50	31 x 67.5 (2)	19.25 x 55.125 (2)
Lowered height (inches)	3.625	3.625	4.563	4.5	4.5	4.5	4.125	4.625	4.25	4.25	4.625
Raised height (inches)	29	29	29	36	36	36	14.6	42	28.75"	29	32
Air pressure requirements (psi)	70-100	70-100	70-100	70-100	70-100	70-100	70-100	70-100	70-100	70-100	-
Features include:											
Portable or fixed	fixed	portable	fixed	fixed	portable	fixed	fixed	fixed	fixed	fixed	fixed
Controller (with 12" of hose)	hand	hand	hand	foot	foot	foot	hand	foot	foot	hand	hand
Adjustable swing arms	•	•		•	•						
Automatic safety arm	•	•	•	•	•	•					
Vertical lift	•	•	•	•	•	•	•	•	•	•	•
Inflation safety valve	•	•	•	•	•	•	•	•	•	•	•
Rubber blocks	•	•		•	•		•	•	•	•	•
Automatic locks - multiple positions	•	•	•	•	•	•					•
Manual lock							•	•	•	•	•
Can be surface or recess mounted	•	N/A	•	•	N/A	•	•	•	•	•	•

BossLifts by Hercules products are proudly made in the USA