

Concentrated Carpet Extraction Cleaner

Low foam extraction cleaner. Use on carpets, rugs and upholstery. Cleans, deodorizes and brightens. Low pH formula recommended for use on all carpet fibers. Dries to an encapsulating crystalline powder. No sticky residue.

DIRECTIONS:

Read cautions and first aid before use. Test for color fastness by applying undiluted solution in an inconspicuous area. Vacuum and rake carpet fibers before use.

Extraction machines:

1. Dilute 2 oz. of solution per gallon of water.
2. Extract carpets & rugs in normal fashion.
3. Do not overwet.
4. Allow to dry.
5. Rake or brush carpet fibers.

Prespray/Traffic lane cleaning:

1. Dilute 12 oz. of solution per gallon of water.
2. Lift carpet fibers with rake.
3. Spray solution onto carpet.
4. Extract in normal fashion.

Bonnet buffing:

1. Dilute with 8-16 parts of water depending on soil level.
2. Spray onto carpet or immerse & wring bonnet dry in mop bucket.
3. Bonnet buff in normal fashion.

GLOBAL FACTS

- Multiple uses
- Low foam extraction cleaner
- Bonnet buffing solution
- Prespray and traffic lane spotter
- Low pH solution - safe on all carpets

MARKETS

- Building Service Contractors
- Hospitality & Lodging
- Healthcare
- Education
- Transportation

SPECIFICATIONS

Color	Light Amber
Scent	Neutral
pH	3.0 - 6.0
Viscosity	Water Thin

REORDER

670284 4x1 Gallon/Case

COMPARE TO

Global Catalog	Zep (B1872694)
Global Catalog	Diversey (B1872683)
Global Catalog	Resolve (B56835)
3M Scotchgard	Extraction Cleaner (70-0713-1225-3)
Spartan	Contempo V (309204)

