


> AXR8

Excellent resistance to solvents and to high temperature
 Excellent resistance to smudge and scratch
 Excellent printing quality


AXR®8 is a high performance resin ribbon designed for the most demanding applications regarding resistance to mechanical aggressions and/or temperature and/or solvents. It is fully compatible with the label materials dedicated to the same high performance applications.




Printing receptor

synthetics	specific
PP ●●●	Polyimide ●●●
PE ●●●	Acrylate ●●●
PET ●●●	

Printer settings



Print resistance



Compliant with the following regulations

REACH / SVHC 1907/2006/EC
Food Contact 1935/2004/EC
Heavy metals 2011/65/EU
California Proposition 65

Your ribbon identity

Colours: ●


Length (m):

Width (mm):

Part number:

Your distributor:

Contact :



axr8

Application fields




Product performance

print quality					
90°Barcode	95	A _a Small characters	95	Logos	95
0°Barcode	100	2D Barcode	98	Blackness	1,6 ODR*
technical resistances					
Heat	250°C 482°F 300°C 572°F	Light/Blue Wool	>7	Solvents	90
Water/Submerge	100	Rubbing	95	Rubtester: 939g, no damage after ... cycles : IPA: 200 Ethanol: 80 Mineral Spirit: 80 Unleaded gasoline 98: 10 Motor oil: 250 Brake fluid: 10	

Product physico-chemical features

product structure	
PET film	Thickness: 4,5 µm
Ink	Resin
Melting point	85°C/185°F
Backcoating	Silicon based
Coefficient of Friction	Kd < 0.2
Ribbon thickness	< 9 µm
The ribbon is anti static build-up treated	



Storage

storage conditions

12 months recommended
20-80 % Humidity Rate, 5-35°C (40-95°F)

Waste management

inkanto rolls and their packaging allow an optimised waste management. For more information please contact ARMOR.

The inkanto benefits



› **Warranty**
This product is guaranteed for life against any manufacturing defect in normal conditions of use and storage.



› **Quality commitment**
Easy to use with guaranteed product performance: the certificate of conformity for your product can be accessed via the flashcode on the box.



› **Easy to identify products:**
The inkanto rolls families are identified by color codes. The roll labels highlight the important information about the product.



› **Your product is delivered with a cleaning wipe**
To clean the print head and maintain the maximum performance of your printer.



› **Packing**
Consistent packaging units depending on the roll dimensions.

A certified and approved production site



Quality, health & safety and environmental systems:
ISO 9001
OHSAS 18001
ISO 14001
ISO 50001 (France only)



Responsible Care
The charter of the International Council of Chemical Associations for improvements in health & safety and the environment.



Global Compact
UN initiative inviting companies to apply fundamental ethical and environmental values.