


> aXR600

Excellent resistance to smudge and scratch
 Excellent printing quality, sensitivity and receptor multi-compatibility
 Good resistance to high temperature


AXR®600 is the standard resin ribbon of the inkanto range for Corner Edge and Near Edge printers. It has become a reference for its sharpness. It is also unequalled as regards to its high level of mechanical resistance and its ability to print at high speed.




Printing receptor

papers	synthetics
Coated ●○○	PP ●●●
Glossy coated ●●○	PE ●●●
	PET ●●●

Printer settings



Print resistance



Compliant with the following regulations

REACH / SVHC 1907/2006/EC
Food Contact 1935/2004/EC
Heavy metals 2011/65/EU
California Proposition 65
Halogen restrictions

Your ribbon identity

Colours: ●


Length (m):

Width (mm):

Part number:


Your distributor:

Contact :



> aXR600

Application fields




Product performance

print quality		
90°Barcode		85
0°Barcode		100
Small characters		90
2D Barcode		100
Logos		95
Blackness		1,7 ODR
technical resistances		
Heat		180°C 356°F
Light/Blue Wool		>7
Solvents		45
Water/Submerge		100
Rubbing		95
Rubtester: 939g, no damage after ... cycles : IPA: 5 Ethanol: 25 Mineral Spirit: 30 Unleaded gasoline 98: nr* Motor oil: 250 Brake fluid: nr* *not recommended		

Product physico-chemical features

product structure	
PET film	Thickness: 4,5 µm
Ink	Resin
Melting point	80°C/176°F
Backcoating	Silicon based
Coefficient of Friction	Kd < 0.2
Ribbon thickness	< 9 µm
The ribbon is anti static build-up treated	



Storage

storage conditions

12 months recommended

20-80 % Humidity Rate, 5-35°C (40-95°F)

Waste management

inkanto rolls and their packaging allow an optimised waste management. For more information please contact ARMOR.

The inkanto benefits



› **Warranty**
This product is guaranteed for life against any manufacturing defect in normal conditions of use and storage.



› **Quality commitment**
Easy to use with guaranteed product performance: the certificate of conformity for your product can be accessed via the flashcode on the box.



› **Easy to identify products:**
The inkanto rolls families are identified by color codes. The roll labels highlight the important information about the product.



› **Your product is delivered with a cleaning wipe**
To clean the print head and maintain the maximum performance of your printer.



› **Packing**
Consistent packaging units depending on the roll dimensions.

A certified and approved production site



Quality, health & safety and environmental systems:
ISO 9001
OHSAS 18001
ISO 14001
ISO 50001 (France only)



Responsible Care
The charter of the International Council of Chemical Associations for improvements in health & safety and the environment.



Global Compact
UN initiative inviting companies to apply fundamental ethical and environmental values.