

Safety Data Sheet

Issue Date: 30-Jan-2009

Revision Date: 23 January 2018

Version 2

1. IDENTIFICATION

Product Identifier

Product Name Lens Cleaning Towelette (LCT)

Other means of identification

SDS # HLC-007W

Product Code 70, 70-1, 70-10, 70BP, 75

Recommended use of the chemical and restrictions on use

Recommended Use Lens cleaner. Instrument care. Water based cleaner.

Details of the supplier of the safety data sheet

Supplier Address

MCR Safety
1255 Schilling Blvd. West
Collierville, TN 38017

Emergency Telephone Number

Company Phone Number 1-508-699-4406
Emergency Telephone (24 hr) INFOTRAC 1-352-323-3500 (International)
1-800-535-5053 (North America)

2. HAZARDS IDENTIFICATION

Appearance Liquid absorbed onto a towelette **Physical State** Solid containing liquid **Odor** Mild alcohol odor

Classification

The information below is for the liquid absorbed onto the wipe when used in an industrial setting. The wipe itself is considered a consumer good and when used as intended is unlikely to present a hazard.

Serious eye damage/eye irritation	Category 2
Specific target organ toxicity (single exposure)	Category 3
Flammable Liquids	Category 2

Hazards Not Otherwise Classified (HNOC)

Causes mild skin irritation

Signal Word

Danger

Hazard Statements

Causes serious eye irritation
May cause respiratory irritation. May cause drowsiness or dizziness
Highly flammable liquid and vapor

**Precautionary Statements - Prevention**

Wash face, hands and any exposed skin thoroughly after handling
 Wear eye/face protection
 Avoid breathing dust/fume/gas/mist/vapors/spray
 Use only outdoors or in a well-ventilated area
 Keep away from heat/sparks/open flames/hot surfaces. — No smoking
 Keep container tightly closed
 Ground/bond container and receiving equipment
 Use explosion-proof equipment
 Use only non-sparking tools
 Take precautionary measures against static discharge
 Wear protective gloves/protective clothing/eye protection/face protection

Precautionary Statements - Response

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
 If eye irritation persists: Get medical advice/attention
 IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin with water/shower
 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing
 Call a poison center or doctor/physician if you feel unwell
 IN CASE OF FIRE: Use CO₂, dry chemical, or foam for extinction

Precautionary Statements - Storage

Store locked up
 Store in a well-ventilated place. Keep container tightly closed
 Keep cool

Precautionary Statements - Disposal

Dispose of contents/container to an approved waste disposal plant

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical Name	CAS No	Weight-%
Isopropyl Alcohol	67-63-0	20-30
Ethylene Glycol Monobutyl Ether	111-76-2	1-10

If Chemical Name/CAS No is "proprietary" and/or Weight-% is listed as a range, the specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. FIRST-AID MEASURES

First Aid Measures

Eye Contact	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. If eye irritation persists: Get medical advice/attention.
Skin Contact	Wash with soap and water. If irritation persists or an allergic reaction occurs, call a physician.

Inhalation	Remove victim to fresh air and keep at rest in a position comfortable for breathing. If breathing is difficult, give oxygen. If breathing has stopped, give artificial respiration. If symptoms persist, call a physician.
Ingestion	Do not induce vomiting. Rinse mouth. Drink plenty of water. Never give anything by mouth to a person who is unconscious or convulsing. Consult a physician.

Most important symptoms and effects

Symptoms	Causes serious eye irritation. Causes mild skin irritation. May cause respiratory irritation. May cause drowsiness or dizziness. May cause nausea, vomiting, stomach ache, and diarrhea. Ingestion may cause central nervous system depression.
-----------------	---

Indication of any immediate medical attention and special treatment needed

Notes to Physician	Treat symptomatically.
---------------------------	------------------------

5. FIRE-FIGHTING MEASURES**Suitable Extinguishing Media**

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable Extinguishing Media Not determined.

Specific Hazards Arising from the Chemical

Flammable.

Hazardous Combustion Products Carbon oxides.

Sensitivity to Mechanical Impact Not sensitive.

Sensitivity to Static Discharge Yes.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES**Personal precautions, protective equipment and emergency procedures**

Personal Precautions Use personal protective equipment as required. Avoid contact with eyes and skin. Remove all sources of ignition.

Environmental Precautions See Section 12 for additional Ecological Information.

Methods and material for containment and cleaning up

Methods for Containment Prevent further leakage or spillage if safe to do so.

Methods for Clean-Up Use personal protective equipment as required. Wipe or soak up with absorbent material for disposal. Pick up and transfer to properly labeled containers.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on Safe Handling

Handle in accordance with good industrial hygiene and safety practice. Avoid contact with skin, eyes or clothing. Wear appropriate personal protective equipment. Keep away from heat, sparks, flame and other sources of ignition (i.e., pilot lights, electric motors and static electricity). Keep out of the reach of children.

Conditions for safe storage, including any incompatibilities

Storage Conditions

Keep away from incompatible materials, open flames, and high temperatures. Keep container tightly closed and store in a cool, dry and well-ventilated place. Keep out of the reach of children.

Incompatible Materials

Strong oxidizing agents. Acids. Chlorinated compounds.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Isopropyl Alcohol 67-63-0	STEL: 400 ppm TWA: 200 ppm	TWA: 400 ppm TWA: 980 mg/m ³ (vacated) TWA: 400 ppm (vacated) TWA: 980 mg/m ³ (vacated) STEL: 500 ppm (vacated) STEL: 1225 mg/m ³	IDLH: 2000 ppm TWA: 400 ppm TWA: 980 mg/m ³ STEL: 500 ppm STEL: 1225 mg/m ³
Ethylene Glycol Monobutyl Ether 111-76-2	TWA: 20 ppm	TWA: 50 ppm TWA: 240 mg/m ³ (vacated) TWA: 25 ppm (vacated) TWA: 120 mg/m ³ (vacated) S* S*	IDLH: 700 ppm TWA: 5 ppm TWA: 24 mg/m ³

Appropriate engineering controls

Engineering Controls

Showers. Eyewash stations. Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/Face Protection

Avoid contact with eyes.

Skin and Body Protection

Protective gloves.

Respiratory Protection

If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

General Hygiene Considerations

Do not eat, drink or smoke when using this product. Remove and wash contaminated clothing before reuse. Provide regular cleaning of equipment, work areas and clothing.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical State
Appearance
Color

Solid containing liquid
Liquid absorbed onto a towelette
Colorless

Odor
Odor Threshold

Mild alcohol odor
No information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	7	
Melting Point/Freezing Point	No information available	
Boiling Point/Boiling Range	No information available	
Flash Point	12 °C / 54 °F	
Evaporation Rate	No information available	
Flammability (Solid, Gas)	Not determined	
Upper Flammability Limits	No information available	
Lower Flammability Limit	No information available	
Vapor Pressure	No information available	
Vapor Density	No information available	
Specific Gravity	No information available	
Water Solubility	No information available	
Solubility in other solvents	No information available	
Partition Coefficient	Not determined	
Auto-ignition Temperature	No information available	
Decomposition Temperature	No information available	
Kinematic Viscosity	Not determined	
Dynamic Viscosity	Not determined	
Explosive Properties	Not determined	
Oxidizing Properties	Not determined	
VOC Content	No information available	

10. STABILITY AND REACTIVITY

Reactivity

Not reactive under normal conditions.

Chemical Stability

Stable under recommended storage conditions.

Possibility of Hazardous Reactions

Hazardous polymerization does not occur.

Hazardous Polymerization	Hazardous polymerization does not occur.
---------------------------------	--

Conditions to Avoid

Heat, flames and sparks. Incompatible Materials.

Incompatible Materials

Strong oxidizing agents. Acids. Chlorinated compounds.

Hazardous Decomposition Products

Carbon oxides.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information

Eye Contact	Causes serious eye damage.
--------------------	----------------------------

Skin Contact	Causes mild skin irritation.
---------------------	------------------------------

Inhalation	Do not inhale.
-------------------	----------------

Ingestion	Do not ingest.
------------------	----------------

Component Information

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Isopropyl Alcohol 67-63-0	= 4396 mg/kg (Rat)	= 12800 mg/kg (Rat) = 12870 mg/kg (Rabbit)	= 72.6 mg/L (Rat) 4 h
Ethylene Glycol Monobutyl Ether 111-76-2	= 470 mg/kg (Rat)	= 2270 mg/kg (Rat) = 220 mg/kg (Rabbit)	= 2.21 mg/L (Rat) 4 h = 450 ppm (Rat) 4 h

Information on physical, chemical and toxicological effects

Symptoms Please see section 4 of this SDS for symptoms.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Carcinogenicity The table below indicates whether each agency has listed any ingredient as a carcinogen. However, the product as a whole has not been tested.

Chemical Name	ACGIH	IARC	NTP	OSHA
Isopropyl Alcohol 67-63-0		Group 3		X
Ethylene Glycol Monobutyl Ether 111-76-2	A3	Group 3		

Legend

ACGIH (American Conference of Governmental Industrial Hygienists)

A3 - Animal Carcinogen

IARC (International Agency for Research on Cancer)

Group 3 IARC components are "not classifiable as human carcinogens"

OSHA (Occupational Safety and Health Administration of the US Department of Labor)

X - Present

STOT - single exposure May cause respiratory irritation. May cause drowsiness or dizziness.

Chronic toxicity Avoid repeated exposure. Contains a known or suspected reproductive toxin.

Numerical measures of toxicity

Not determined

12. ECOLOGICAL INFORMATION**Ecotoxicity**

The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

Component Information

Chemical Name	Algae/aquatic plants	Fish	Toxicity to microorganisms	Crustacea
Isopropyl Alcohol 67-63-0	1000: 96 h Desmodemus subspicatus mg/L EC50 1000: 72 h Desmodemus subspicatus mg/L EC50	9640: 96 h Pimephales promelas mg/L LC50 flow-through 11130: 96 h Pimephales promelas mg/L LC50 static 1400000: 96 h Lepomis macrochirus µg/L LC50		13299: 48 h Daphnia magna mg/L EC50
Ethylene Glycol Monobutyl Ether 111-76-2		1490: 96 h Lepomis macrochirus mg/L LC50 static 2950: 96 h Lepomis macrochirus mg/L LC50		1698 - 1940: 24 h Daphnia magna mg/L EC50 1000: 48 h Daphnia magna mg/L EC50

Persistence/Degradability

Not determined.

Bioaccumulation

Not determined.

Mobility

Chemical Name	Partition Coefficient
Isopropyl Alcohol 67-63-0	0.05
Ethylene Glycol Monobutyl Ether 111-76-2	0.81

Other Adverse Effects

Not determined

13. DISPOSAL CONSIDERATIONS**Waste Treatment Methods****Disposal of Wastes**

This material, as supplied, is not a hazardous waste according to Federal regulations (40 CFR 261). This material could become a hazardous waste if it is mixed with or otherwise comes in contact with a hazardous waste, if chemical additions are made to this material, or if the material is processed or otherwise altered. Consult 40 CFR 261 to determine whether the altered material is a hazardous waste. Consult the appropriate state, regional, or local regulations for additional requirements.

Contaminated Packaging

Disposal should be in accordance with applicable regional, national and local laws and regulations.

California Hazardous Waste Status

Chemical Name	California Hazardous Waste Status
Isopropyl Alcohol 67-63-0	Toxic Ignitable

14. TRANSPORT INFORMATION**Note**

Please see current shipping paper for most up to date shipping information, including exemptions and special circumstances.

DOT

Not regulated

IATA

Not regulated

IMDG

Not regulated

15. REGULATORY INFORMATION**International Inventories**

Chemical Name	TSCA	DSL	NDSL	EINECS	ELINCS	ENCS	IECSC	KECL	PICCS	AICS
Isopropyl Alcohol	Present	X		Present		Present	X	Present	X	X
Ethylene Glycol Monobutyl Ether	Present	X		Present		Present	X	Present	X	X

Legend:*TSCA - United States Toxic Substances Control Act Section 8(b) Inventory**DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List**EINECS/ELINCS - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances**ENCS - Japan Existing and New Chemical Substances**IECSC - China Inventory of Existing Chemical Substances**KECL - Korean Existing and Evaluated Chemical Substances**PICCS - Philippines Inventory of Chemicals and Chemical Substances**AICS - Australian Inventory of Chemical Substances***US Federal Regulations****CERCLA**

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355).

SARA 311/312 Hazard Categories

Acute Health Hazard	Yes
Chronic Health Hazard	Yes
Fire Hazard	No
Sudden Release of Pressure Hazard	No
Reactive Hazard	No

SARA 313

Chemical Name	CAS No	Weight-%	SARA 313 - Threshold Values %
Isopropyl Alcohol - 67-63-0	67-63-0	27	1.0
Ethylene Glycol Monobutyl Ether - 111-76-2	111-76-2	3.72	1.0

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

US State Regulations**California Proposition 65**

This product does not contain any Proposition 65 chemicals.

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania
Isopropyl Alcohol 67-63-0	X	X	X
Ethylene Glycol Monobutyl Ether 111-76-2	X	X	X

16. OTHER INFORMATION

<u>NFPA</u>	Health Hazards	Flammability	Instability	Special Hazards
	2	3	Not determined	Not determined
<u>HMIS</u>	Health Hazards	Flammability	Physical Hazards	Personal Protection
	2	3	0	B- Safety Glasses, Gloves

Issue Date: 30-Jan-2009
Revision Date: 23-Jan-2018
Revision Note: Update

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet