


## OP-916 NTEP HEAVY DUTY FLOOR SCALES



LED



LCD

OP-900-MS Indicator

### FEATURES

- Painted rugged diamond deck tread plate construction
- Anti-corrosion, baked on powder paint
- Channel construction for superior strength
- Painted mild steel junction box
- Side access to junction box to minimize water access
- Four NTEP certified alloy steel load cells
- Load cell capacity is 2X the scale capacity for a 200% overload protection
- Four adjustable alloy steel ball capture support feet
- 20' heavy duty stainless steel shielded cable
- Factory pre-calibrated for quick setup

### OPTIONS/ACCESSORIES:

- Access ramps
- Pit frames
- Impact Protection
- Portability frames
- Thermal printer
- Stand for indicator
- Large Display
- Data logging software
- Remote junction box
- Wireless option
- Explosion proof option

| PART#           | PLATFORM SIZE      | CAPACITY                     | NTEP | SHIP WEIGHT |
|-----------------|--------------------|------------------------------|------|-------------|
| OP-916-2424-1K  | 2' x 2' x 4.2" H   | 1,000 lb x 0.2 lb / 500 kg   | Yes  | 82 lbs      |
| OP-916-2424-5K  | 2' x 2' x 4.2" H   | 5,000 lb x 1 lb / 2,500 kg   | Yes  | 82 lbs      |
| OP-916-2x3-5K   | 2' X 3' X 4.2" H   | 5,000 lb x 1 lb / 2,500 kg   | Yes  | 94 lbs      |
| OP-916-3030-5K  | 30" x 30" x 4.2" H | 5,000 lb x 1 lb / 2,500 kg   | Yes  | 98 lbs      |
| OP-916-3x3-5K   | 3' x 3' x 4.2" H   | 5,000 lb x 1 lb / 2,500 kg   | Yes  | 194 lbs     |
| OP-916-4x4-2K   | 4' x 4' x 4.2" H   | 2,000 lb x .5 lb / 1,000 kg  | Yes  | 270 lbs     |
| OP-916-4x4-5K   | 4' x 4' x 4.2" H   | 5,000 lb x 1 lb / 2,500 kg   | Yes  | 270 lbs     |
| OP-916-4x4-10K  | 4' x 4' x 4.2" H   | 10,000 lb x 2 lb / 5,000 kg  | Yes  | 280 lbs     |
| OP-916-4x4-20K  | 4' x 4' x 4.75" H  | 20,000 lb x 5 lb / 10,000 kg | Yes  | 390 lbs     |
| OP-916-4x5-5K   | 4' x 5' x 4.2" H   | 5,000 lb x 1 lb / 2,500 kg   | Yes  | 340 lbs     |
| OP-916-4x5-10K  | 4' x 5' x 4.2" H   | 10,000 lb x 2 lb / 5,000 kg  | Yes  | 340 lbs     |
| OP-916-5x5-5K   | 5' x 5' x 4.2" H   | 5,000 lb x 1 lb / 2,500 kg   | Yes  | 400 lbs     |
| OP-916-5x5-10K  | 5' x 5' x 4.2" H   | 10,000 lb x 2 lb / 5,000 kg  | Yes  | 420 lbs     |
| OP-916-5x5-20K  | 5' x 5' x 4.75" H  | 20,000 lb x 5 lb / 10,000 kg | Yes  | 512 lbs     |
| OP-916-4x6-5K   | 4' x 6' x 4.2" H   | 5,000 lb x 1 lb / 2,500 kg   | Yes  | 480 lbs     |
| OP-916-4x6-10K  | 4' x 6' x 4.2" H   | 10,000 lb x 2 lb / 5,000 kg  | Yes  | 480 lbs     |
| OP-916-4x8-5K   | 4' x 8' x 4.2" H   | 5,000 lb x 1 lb / 2,500 kg   | Yes  | 500 lbs     |
| OP-916-4x8-10K  | 4' x 8' x 4.2" H   | 10,000 lb x 2 lb / 5,000 kg  | Yes  | 500 lbs     |
| OP-916-5x7-10K  | 5' x 7' x 4.2" H   | 10,000 lb x 2 lb / 5,000 kg  | Yes  | 540 lbs     |
| OP-916-5x7-20K  | 5' x 7' x 4.75" H  | 20,000 lb x 5 lb / 10,000 kg | Yes  | 725 lbs     |
| OP-916-5x8-10K  | 5' x 8' x 4.5" H   | 10,000 lb x 2 lb / 5,000 kg  | Yes  | 625 lbs     |
| OP-916-6x6-20K  | 6' x 6' x 4.75" H  | 20,000 lb x 5 lb / 10,000 kg | Yes  | 800 lbs     |
| OP-916-7x7-20K  | 7' x 7' x 4.75" H  | 20,000 lb x 5 lb / 10,000 kg | Yes  | 1,000 lbs   |
| OP-916-7x7-30K  | 7' x 7' x 5" H     | 30,000 lb x 5 lb / 15,000 kg | No   | 1,130 lbs   |
| OP-916-7x10-20K | 7' x 10' x 5" H    | 20,000 lb x 5 lb / 10,000 kg | No   | 1,450 lbs   |

CUSTOM SIZES AVAILABLE

