

HB - 25



VALUEMUFF™ DIELECTRIC EAR MUFF WITH INDESTRUCTIBLE HEADBAND AND SMART FOLD-OUT DESIGN
Ref. WELHB25_



Product specifications

The ValueMuff™ is our lightweight ear muff with an unbreakable multi-position headband. Rugged, fully dielectric construction protects workers from electrical shocks and shorts.

Headband: Acetyl
Ear Cup: ABS
Foam Absorber: Polyurethane
Ear Cushion: PVC

COLOR

Blue, Orange

SIZE

No size

Product Use - Risks



Noise



Agriculture / Green areas
craftman



Construction / Civil engineering



Second work /



Heavy industry



Light industry



Services / Logistics



Hygiene environment



Oil / Gas



Mining



Wind/Energy

Product's highlights & user's benefits

Comfortable, yet tough unbreakable multi-position headband.

Exclusive ELVEX® "smart fold-out" design, muffs fold-out and rest comfortably around neck when not in use.

Self-aligning suspension on headband for quick fitting and adjustment.

Soft, pliable SuperSeal™ ear cushions are long lasting and resist body oil and sweat.

Multi-position use with or without optional support strap for compatibility when worn with other hats.

Certifications and Standards

USA STANDARDS



ANSI S12.6 Hearing Protection Attenuation Standard - ANSI S12.6





ANSI S3.19 American National Standards Institute
25 NRR: NRR – (Noise Reduction Rating - Noise Reduction Rating)



89/686/EEC PPE DIRECTIVE

EN352-1 Earing protection : Ear-muff
28 SNR: Standard noise reduction
H 30: High frequency attenuation
M 25: Medium frequency attenuation
L 17: Low frequency attenuation

References

References	Bar code	COLOR	SIZE		
WELHB25	7292948225000	Blue	No size	24	-
WELHB25LIOI	00	Blue	No size	24	-
WELHB25ORG	3295249224240	Orange	No size	24	-