


A low-profile headlamp with Class I, Div 1 safety ratings. Three lighting modes cover a variety of tasks: spot for a focused beam, flood for soft area illumination that won't tire your eyes and spot/flood combo for even more light output.



Spot/Flood Combo = 235 lumens


 Flood LED  
 Spot LED


Lightweight, low-profile design



Includes rubber strap and 3M™ Dual Lock™ for strapless mounting to hard hats



Spot and flood beams: – Spot: 160 lumens; 1,320 candela; 73m beam; runs 5 hours – Flood: 160 lumens; 100 candela; 20m beam; runs 5 hours – Spot/flood combo: 235 lumens; runs 4.75 hours
45° tilting head
Tough, polycarbonate thermoplastic construction with elastomer over mold; Unbreakable polycarbonate lenses; recessed to prevent scratches

IPX7 waterproof; 2m impact resistance tested
Class I, II, Division 1, Groups A, B, C, D, E, F, G; Class III; Class 1, Zone 0, Group IIC, Exia; T-Code: T4
3.5 oz (99.2 grams) with batteries
Limited Lifetime Warranty Visit <a href="http://www.streamlight.com">www.streamlight.com</a> for full warranty information
#61424 - Enduro Pro - alkaline batteries, elastic headstrap, rubber hard hat strap, and 3M™ Dual Lock™ - Box - Yellow