

POWERTEC 828HD

Shreds Hard Drives | SSDs | Cell Phones | Optical Media | Paper

Special Features



Security Level



Security Level



Sheet Capacity



Cell Phones




Chain Driven Motor



Jam Protection



Self-Clean Shredder



Precision Engineered


The PowerTEC 828 HD Hard Drive Combination Shredder is the perfect machine for safely destroying hard drives, SSDs, cell phones, optical media, and paper. It features a powerful 4.5 Hp. chain driven motor, automatic jam protection, and simple push button operation. This multimedia shredder is rated for Security Level H-4/P-3 destruction, and is precision engineered to provide many years of trouble-free operation.



Destroys devices and paper for complete data security.

Features/Benefits

- Powerful hard drive and multimedia combination shredder
- Security Level H-4 / P-3 for the destruction of sensitive information
- Mighty 4.5 Hp continuous duty motor with chain driven operation
- Automatic jam protection- Machine cycles through forward and reverse until shredding is complete
- LED keypad with easy-to-use controls for simple operation
- Rubber shock mounts suspend the cutting head and reduce vibration
- Self-cleaning mode ensures optimal performance
- For safety, the shredder stops when the doors are opened



Aggressive cutting cylinders shred up to 100 sheets at a time.



828HD Specifications

Security Level	NSA Approved	Capacity	Shred Size paper media	Waste Volume paper media	Feed Width paper media
P-3 H-4		100 / 110	5mm x 70mm 40mm x 40-90mm	30 gal. 26 gal.	11.8" 4.7"
Motor	Decibel Level	Warranty	Dimensions length x width x height	Weight	Power Supply
4.5 Hp	60	1 Year	38.25" x 33.5" x 46.5"	1,257 lbs	220v 3 Phase