

**1 STANDARD DUTY**  
300 LBS | 135 KG

**ENCLOSED CARTS | STAINLESS STEEL**

*The dependability of Stainless Steel with a smartly styled exterior finish combines the best of both worlds.*

- Choose from a variety of popular vinyl and laminate finishes to match your décor and impress your guests (Walnut vinyl is standard)
- Stainless steel interior prevents odor retention from spills
- All welded angle leg construction is more durable and easy to clean
- Reinforced, hemmed front on 22 gauge shelves add strength where the cart is most vulnerable to stress


**FINISHES (PAGE 57):**

- GROUP 1 vinyl finishes: Black, Light Maple and Red Maple
- GROUP 2 finishes
- GROUP 3 Custom laminate finishes



**FACTORY INSTALLED OPTIONS (PAGE 55):**

- Strip bumpers
- Perimeter bumpers
- 2-5" fixed, 2-5" swivel casters
- All 5" cushion tread
- 2 brake and 2 no brake casters
- Sta-Clean® vinyl cover
- Hinged doors
- Door w/lock



Accessories include detachable plastic silverware and waste boxes.



**HINGED DOORS OR DOOR W/LOCK AVAILABLE ON:**

610, 615, 622, 626, 644, 646, 810, 815, 822, 844

Factory Option: Hinged Doors



Model #615  
Shown in Gray Sand



Model #610  
Shown in standard Walnut vinyl

**Freight Class: 125**  
Ships in: 4 days or less!

Model	# of Shelves	Shelf Size	Shelf Clearance	Overall Size			Case Weight Lbs. (Kg)	Case Cube Cu. ft. (m <sup>3</sup> )
				W	L	H		
<b>Stainless Steel Top Shelf - 3 Edges Up, 1 Down</b>								
610	3	15-1/2" x 24" (394 x 610)	12-3/8" (314)	16-1/2" (419)	27-3/4" (705)	32-3/4" (832)	40 (18.1)	15.8 (.61)
615	4	15-1/2" x 24" (394 x 610)	8" (203)	16-1/2" (419)	27-3/4" (705)	32-3/4" (832)	43 (19.5)	15.8 (.61)

Measurements in ( ) denote metric millimeters, unless otherwise specified. Lake-Glide® Casters: 3-1/2" (89) - All swivel.