

### DP4 Face Shield Series



S32010



S32151

### ORDERING INFORMATION

Product No.	Window/Flip Visor	Weight	Dimensions	Application
S32010	Clear Anti-Fog Window	0.78 lbs (12 oz)	9" x 12.125" x 0.060" (Clear Window)	• Standard
S32151	Clear Anti-Fog Window and Shade 5 IR Flip Front Window	0.87 lbs (14 oz)	9" x 12.125" x 0.060" (Clear Window) 4.375" x 9.25" x .070" (Flip Front)	• Oxy/Acetylene Cutting • Brazing • Plasma Cutting
S32161	Clear Anti-Fog Window and Shade 6 IR Flip Front Window	0.87 lbs (14 oz)	9" x 12.125" x 0.060" (Clear Window) 4.375" x 9.25" x .070" (Flip Front)	• Oxy/Acetylene Cutting • Brazing • Plasma Cutting
S32161B	Clear Anti-Fog Window and Shade 6 IR Cobalt Flip Front Window	0.87 lbs (14 oz)	9" x 12.125" x 0.060" (Clear Window) 4.375" x 9.25" x .070" (Flip Front)	• Oxy/Acetylene Welding (Aluminum and Cast Iron) • Metal and Glass Furnace Foundry Work
S32181	Clear Anti-Fog Window and Shade 8 IR Flip Front Window	0.87 lbs (14 oz)	9" x 12.125" x 0.060" (Clear Window) 4.375" x 9.25" x .070" (Flip Front)	• Oxy/Acetylene Welding • Plasma Cutting

Materials	Description
Crown	Nylon
Windows	High impact resistant molded polycarbonate
Headgear	Nylon (headgear includes head band for comfort)

#### Description and Performance:

Rugged, polycarbonate clear anti-fog window is impact & chemical splash resistant. The shield curves naturally to fit facial contours, ensuring reliable protection from splash, particles, and flying debris. Ratchet headgear suspension allows user to adjust size and tighten at the turn of a knob. Headgear includes a sweat-absorbent head band for added comfort. All parts are replaceable.

**Sellstrom Manufacturing Co.**  
Elgin, IL 60123  
Phone: (800) 323-7402  
Fax: (847) 358-8564  
www.sellstrom.com

**Operating Temperature:** 23°F to 131°F (-5°C to 55°C)

**Standards Compliance:** Meets ANSI Z87+, CE certified to EN 166 & EN 170 and CUL certified to meet CSA Z94.3