



ergotron®

## StyleView® 40 (SV40) – Non-Powered Documentation Cart with Optional Drawers

Choose the StyleView medical cart that best meets your caregiving needs, style and workflow. Our market-leading StyleView carts include all the features that caregivers ask for, with all the open architecture and quality construction that IT departments require.



SV40 Laptop cart

- Innovative documentation cart for the point of care
- Non-powered with add-on power options available
- Two choices of display mounts
- Truly ergonomic design
- Lightweight cart with a small footprint
- Customize with storage and accessories
- Ships fully assembled
- 5-year warranty

### Highlights

- Effortlessly maneuver to the point of need with ultra-smooth gliding casters
- Ergonomically accommodates the widest height range of users when sitting or standing
- Offers effortless sit-stand height adjustment using patented Constant Force™ technology
- Compact footprint fits in space-constrained areas
- Open-architecture design accommodates multiple configurations: Closed notebooks with monitor, CPU and monitor, thin clients, tablets, all-in-one computers and future hardware upgrades
- Passes Ergotron's 10,000-cycle motion test, ensuring at least five years of trouble-free height adjustment
- Supports comfortable typing with an adjustable back-tilt keyboard tray
- Tested and fully certified for patient, caregiver and facility safety

### Choose display mount type:



Laptop:  
#SV40-6100-0



LCD Pivot:  
#SV40-6300-0

### ERGONOMICS:

Ergonomic back-tilt keyboard tray with a left or right mouse tray keeps wrists in a neutral position to avoid repetitive-stress injuries while increasing comfort and productivity.

Designed for users 5'0" to 6'1" (152 to 185 cm) tall and for ongoing sitting or standing applications.

Large adjustment range helps shorter and taller users work comfortably and productively whether seated or standing.

### SAFETY:

Tested to UL/EN/IEC specifications for enhanced patient safety.

Durable, easy-to-clean exterior composed of aluminum, high-grade plastic and zinc-plated steel promotes infection control.

Includes lockable and ventilated storage for closed notebook, thin client or CPU with heavy-duty keys and locks.

Four ultra-smooth gliding casters create easy push-pull mobility with two locking casters for stability.

Provides additional security with CPU lock inside the storage compartment.

(continued)

**DIMENSIONS AND WEIGHTS:**

LCD Pivot: Storage compartment for closed notebook, thin client or CPU: 17.75" W x 14.75" D x 4" H (45W x 37,5D x 10,1H cm); larger computers can mount to rear of cart with optional Universal CPU Holder (#80-105-064)

Compact wheel-to-wheel base dimensions: 17" x 21" (43 x 53,3 cm)

Cart weight: 54 lb (24,5 kg)


Shipping dimensions: 53" D x 34" W x 36" H (135D x 89W x 91H cm)

Shipping weight: 83 lbs (38 kg)

**PRODUCTS INCLUDE:**

LCD Pivot\*, worksurface, secure CPU compartment, scanner holder bracket, mouse holder, wrist rest, back-tilt keyboard tray, left/right mouse tray, cable storage, four casters (two locking); 5-year warranty

\* Laptop version does not include a LCD Pivot



Durable, easy-to-clean exterior composed of aluminum, high-grade plastic and zinc-plated steel

- ① Supports displays up to 24" and provides 25 degrees of tilt and 90° rotation
  - Laptop: Laptop and worksurface adjust 20" (51 cm) in tandem
  - LCD Pivot: LCD and worksurface adjust 20" (51 cm) in tandem; LCD Pivot adjusts 5" (13 cm) independently; maximum LCD height adjustment = 25" (63 cm) (Note: Portrait screen orientation may be incompatible with widescreen displays >19")
- ② Scanner holder bracket
- ③ Spacious worksurface: 22.4" W x 19.75" D (56,7W x 50,2D cm)
- ④ Back-tilt keyboard tray, wrist rest and mouse holder
- ⑤ T-slot channel interface on the column allows you to integrate drawers and accessories
- ⑥ Four 4" (10,2 cm) casters; two front casters are lockable
- ⑦ Wheel-to-wheel base dimensions: 17" x 21" (43 x 53,3 cm)

	Typical LCD Size	Weight Capacity	Lift	Tilt	Pan	Rotation	VESA
Non-Powered SV40	LCD Pivot	≤ 24" 35 lbs (15,9 kg) See website	25" (63,5 cm)	25°	24°	90°	MIS-D
	Laptop	≤ 17.3" 18 lbs (8,2 kg) See website	20" (51 cm)	—	—	—	—
Includes secure CPU compartment							
5-year warranty for mechanical components							

SV40 LCD Pivot cart

**SEVERAL STORAGE OPTIONS AND ACCESSORIES AVAILABLE:**



© 2019 Ergotron, Inc. 03/12/2019-EA Literature made in the U.S.A.  
Ergotron devices are not intended to cure, treat, mitigate or prevent any disease. StyleView is a registered trademark of Ergotron in the U.S.A. and China. **Content is subject to change without notification.**

Americas Sales and Corporate Headquarters	EMEA Sales	APAC Sales	Worldwide OEM Sales
St. Paul, MN USA (800) 888-8458 +1-651-681-7600 www.ergotron.com sales@ergotron.com	Amersfoort, The Netherlands +31 33 45 45 600 www.ergotron.com info.eu@ergotron.com	Tokyo, Japan www.ergotron.com apaccustomerservice@ergotron.com	www.ergotron.com info.oem@ergotron.com

