



1U Rack-Mount Power Strip, 120V, 20A, L5-20P, 12 Outlets (6 Front-Facing, 6-Rear-Facing) 15 ft. (4.57 m) Cord

MODEL NUMBER: RS-1215-20T



Highlights

- Designed for standard 19-in. racks (1U high)
- 12 NEMA5-15/20R outlets (6 front/6 rear)
- 15-ft. (4.57 m) cord with locking NEMA L5-20P input plug
- 20A circuit breaker

Description

Tripp Lite's RS-1215-20T Power Strip offers 20A capacity AC power distribution in a versatile multi-mount cabinet. Detachable mounting flanges are configurable for rackmount, wallmount and under-counter installation. Uses only 1 rack space (1U) when installed in any 19-in. rack meeting EIA standards. Unfiltered electrical pass-through makes RS-1215-20T ideal for distributing alternate waveform UPS or generator power in rack enclosures, network closets and more. Includes 12 NEMA5-15/20R outlets (6 front/6 rear), 15-ft. (4.57 m) AC power cord with locking NEMA L5-20P input plug and lighted switch with cover that prevents risk of accidental turn-off.

PLUG/OUTLETS: Input: NEMA L5-20P Output: 12 x NEMA5-15/20R (6 front/6 rear)

ELECTRICAL: 120V AC, 50/60Hz, 20A (Requires NEMA 5-20R wall receptacle)

FORMAT: 19-in. rackmount (uses 1 rack space/1U), wallmount, under-counter and more

Features

- Versatile all-metal cabinet with detachable mounting flanges allows rackmount, wallmount, undercounter and other creative mounting options
- Uses one rack space (1U) in standard 19-in. rack ("zero U" mounting possible in many racks)
- Unfiltered electrical pass-through reliably distributes alternate waveform AC power from UPS or generator to supported equipment
- 12 x NEMA5-15/20R output receptacles (6 front/6 rear)
- 15-ft. (4.57 m) AC cord with NEMA L5-20P input plug
- Lighted power switch confirms power on/off status
- Snap-in switch guard prevents accidental turn-off
- 20A electrical capacity with circuit breaker
- 120V AC, 50/60Hz electrical compatibility

Specifications



OVERVIEW	
UPC Code	037332119704
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	20A 120V dedicated line
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA L5-20P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	2400
Output Receptacles	(12) 5-15/20R
Circuit Breaker (amps)	20
Overload Protection	20A circuit breaker
Transformer Accommodation	(5) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted power switch
Locking Switch Cover	Yes
PHYSICAL	
Color	Black
Antimicrobial Coating	No
Power Cord Color	Black
Form Factors Supported	1U rackmount, wallmount
Housing Color	Black
Included Mounting Accessories	Rackmount flanges
Integrated Keyhole Mounting Slots	No
Material of Construction	Metal
Outlets Measurement (Center to Center)	Distance between Front outlets = 51.6mm; Distance between Rear outlets = 71.1mm
Receptacle Color	Black



Shipping Dimensions (hwd / cm)	23.62 x 6.60 x 51.31
Shipping Dimensions (hwd / in.)	9.30 x 2.60 x 20.20
Shipping Weight (kg)	2.68
Shipping Weight (lbs.)	5.90
Unit Dimensions (hwd / cm)	4.3 x 44.4 x 11.4
Unit Dimensions (hwd / in.)	1.75 x 17.5 x 4.5
Unit Weight (kg)	2.45
Unit Weight (lbs.)	5.4
STANDARDS & COMPLIANCE	
Approvals	UL-recognized (USA)/cUR (Canada)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>