

# KÄRCHER

makes a difference



## DIRTY FLOORS FEAR THIS POWERHOUSE

Cover more ground, faster with incredibly productive ride-on scrubber.

# Dirt does not stand a chance.

Eliminate soils fast with several productive scrub deck options for the B 250. It is built on a robust tubular steel frame to handle even the toughest operating conditions. We know that if you are looking at a machine this size you want ultimate productivity so we include large batteries and a huge solution tank to ensure long run times. The intuitive one-dial control and large color LCD screen make this beast of a scrubber surprisingly easy to use.



## 1 Calling this machine productive is an understatement

- Best in class practical productivity of up to 48,440 ft<sup>2</sup>/hr
- The brush deck is available in two widths to suit any need
- Save time and avoid pre-sweeping with optional integrated side brooms

## 2 Easy-to-use and easy-to-drive

- The short wheelbase and narrow body ensure great maneuverability for a machine of this size
- Simple to drive, one-dial operation
- No intensive training required
- Operators will appreciate the comfortable seat during long shifts

## 3 Maintenance is a breeze

- Tool-free brush removal
- With the automatic filling system, other tasks can be carried out while the tank automatically fills itself

## 4 Get it done in less time

- Long runtimes in standard mode
- Ecoefficiency mode for even longer runtimes and less chemical consumption

## 5 Designed for the real world

- Integrated brush head impact protection for durability
- Color coded controls makes training easy

# Technical specifications and order numbers.



*Pictured side brooms are optional*

**B 250 R Bp with R 100 head**

**B 250 R Bp with D 100 head**

**B 250 R Bp with R 120 head**

TECHNICAL SPECIFICATIONS			
Cleaning path	in	39	47
Brush quantity		2	2
Brush diameter	in	5	5
Squeegee width	in	42	56
Tank capacity (solution/recovery)	gal	66/66	66/66
Operating noise level (standard/eco!)	dB(A)	73/65	73/65
Total machine battery voltage	V	36	36
Down pressure	lbs	291	309
Brush speed (min/max)	rpm	600/1,250	600/1,250
Weight with batteries	lbs	2,756	2,800
Dimensions (L x W x H)	in	75 x 42 x 61	75 x 42 x 61
Productivity (practical/theoretical)	ft <sup>2</sup> /hr	40,365/64,585	48,440/77,500
Minimum turning radius	in	84	84
Climbing ability (scrubbing/transport)	%	12/15	12/15
Max speed (scrubbing/transport)	mph	3.7/5	3.7/5

## EQUIPMENT

Order No.	Description
9.841-298.0	B 250 R Bp, R 100 cylindrical scrub deck, 36 V/344 Ah wet batteries, shelf charger, curved squeegee, red brushes
9.841-299.0	B 250 R Bp, R 100 cylindrical scrub deck, 36 V/335 Ah AGM batteries, shelf charger, curved squeegee, red brushes
9.841-300.0	B 250 R Bp, R 100 cylindrical scrub deck, 36 V/650 Ah steel case wet batteries, shelf charger, curved squeegee, red brushes
9.841-301.0	B 250 R Bp, R 100 cylindrical scrub deck, 36 V/650 Ah steel case wet batteries, H.E. shelf charger, curved squeegee, red brushes
9.841-306.0	B 250 R Bp, R 100 cylindrical scrub deck, 36 V/344 Ah batteries, shelf charger, curved squeegee, red brushes, two side brooms
9.841-307.0	B 250 R Bp, R 100 cylindrical scrub deck, 36 V/335 Ah AGM batteries, shelf charger, curved squeegee, red brushes, two side brooms
9.841-308.0	B 250 R Bp, R 100 cylindrical scrub deck, 36 V/650 Ah steel case wet batteries, shelf charger, curved squeegee, red brushes, two side brooms
9.841-309.0	B 250 R Bp, R 100 cylindrical scrub deck, 36 V/650 Ah steel case wet batteries, H.E. shelf charger, curved squeegee, red brushes, two side brooms
9.841-302.0	B 250 R Bp, R 120 cylindrical scrub deck, 36 V/344 Ah batteries, shelf charger, curved squeegee, red brushes
9.841-303.0	B 250 R Bp, R 120 cylindrical scrub deck, 36 V/335 Ah AGM batteries, shelf charger, curved squeegee, red brushes
9.841-304.0	B 250 R Bp, R 120 cylindrical scrub deck, 36 V/650 Ah steel case wet batteries, shelf charger, curved squeegee, red brushes
9.841-305.0	B 250 R Bp, R 120 cylindrical scrub deck, 36 V/650 Ah steel case wet batteries, H.E. shelf charger, curved squeegee, red brushes
9.841-310.0	B 250 R Bp, R 120 cylindrical scrub deck, 36 V/344 Ah batteries, shelf charger, curved squeegee, red brushes, two side brooms
9.841-311.0	B 250 R Bp, R 120 cylindrical scrub deck, 36 V/335 Ah AGM batteries, shelf charger, curved squeegee, red brushes, two side brooms
9.841-312.0	B 250 R Bp, R 120 cylindrical scrub deck, 36 V/650 Ah steel case wet batteries, shelf charger, curved squeegee, red brushes, two side brooms
9.841-313.0	B 250 R Bp, R 120 cylindrical scrub deck, 36 V/650 Ah steel case wet batteries, H.E. shelf charger, curved squeegee, red brushes, two side brooms
9.841-361.0	B 250 R Bp, D 100 disc scrub deck, 36 V/344 Ah wet batteries, shelf charger, shelf charger, curved squeegee, red brushes
9.841-362.0	B 250 R Bp, D 100 disc scrub deck, 36 V/335 Ah AGM batteries, shelf charger, shelf charger, curved squeegee, red brushes
9.841-363.0	B 250 R Bp, D 100 disc scrub deck, 36 V/650 Ah steel case wet batteries, shelf charger, shelf charger, curved squeegee, red brushes
9.841-364.0	B 250 R Bp, D 100 disc scrub deck, 36 V/650 Ah steel case wet batteries, shelf charger, H.E. shelf charger, curved squeegee, red brushes

## SERVICES

Order No.	Description
<input type="checkbox"/> 7.000-270.0	Fleet one year premium subscription

■ Included  Optional

## ACCESSORIES

For a list of available accessories please refer to the Kärcher floor care catalog available through customer care with order number 9.807-518.0.

Please contact us for more information:

**North America**

4555 Airport Way  
Denver, CO 80239 U.S.A.

Phone +1 800 444-7654  
Fax +1 866 271-0520

**Canada**

6535 Millcreek Drive  
Unit 67  
Mississauga, ON L5N 2M2 Canada

Phone +1 905 672-8233  
Fax +1 905 672-3155

[www.karcher.com/us](http://www.karcher.com/us)