

Model C3236

Washdown Check Weigher



- **Usability**– Fully washdown catering scale suitable for busy food preparation areas/ kitchens or portion control stations where accuracy is important
- **Capacity**–
6 lb x 0.005 lb / 3 kg x 0.0002 kg
15 lb x 0.001 lb / 7 kg x 0.0005 kg
30 lb x 0.002 lb / 15 kg x 0.001 kg
- **Display**– Fast and easy-to-read 0.6" / 15 mm high red LED display with easy-to-see low, ok and high annunciators
- **Power**– AC adapter with built-in rechargeable battery with up to 62 hours of battery life between charges
- **Platform Dimension (L x W)**–
7.4" x 10" / 190 mm x 255 mm

VALUE IN
WEIGHING

C3236 Washdown Check Weigher

Features

The C3236 is a fully washdown, stainless steel scale ideal for most general purpose weighing, check weighing or portion control applications. Designed for speed and efficiency with limited operator training required, the C3236 is ideal for applications where food preparation or portion control accuracy is essential.

Construction: With a food grade 304 stainless steel housing and top pan and IP68 (NEMA4X) water ingress protection, this scale is easy-to-clean and ideal for use in most washdown environments.

General Weighing Mode: The clear, easy-to-read display allows operators to quickly and easily view weight data before pressing tare between ingredients.

Check Weighing Mode: Ideal for repetitive weighing applications. It can easily be set so the operator can quickly tell if the weight is within a known tolerance with the low, accept, high annunciators and audio alarm.

Operator Keys: Four easy-to-use keys make the scale easy to set up with minimal training requirements.

The C3236 comes standard with a detachable AC power adapter and a built-in rechargeable battery that provides up to 62 hours of battery life between charges. The built-in auto off feature helps prolong battery life when not in use.



a division of Avery Weigh-Tronix, LLC

Specifications

Capacity:

6 lb x 0.0005 lb / 3 kg x 0.0002 kg

15 lb x 0.001 lb / 7 kg x 0.0005 kg

30 lb x 0.002 lb / 15 kg x 0.001 kg

Accuracy: 0.04% at full load

Unit: lb, kg

Main Functionality: General weighing and check weighing with audio low, ok and high buzzer

Display: Large 1.2" x 3.5" / 30 mm x 90 mm red LED display with five 0.6" / 15 mm high digits

Operator Keys: On/Zero/Tare, Function, Unit, Off

Power: Removable AC power adapter (included) along with a built-in rechargeable lead acid battery

Battery Life: Up to 62 hours

Tare: 100%

Operating Temperature:

14° F to 104° F / -10° C to 40° C

Scale Dimension (L x W x H):

13" x 11.4" x 4.3" / 330 mm x 290 mm x 110 mm

Platform Dimension (L x W):

7.5" x 10" / 190 mm x 255 mm

Product Weight: 10.5 lb / 4.8 kg

Packaging Dimension (L x W x H):

14.4" x 13.2" x 5.7" / 365 mm x 335 mm x 145 mm

Shipping Weight: 7.7 lb / 3.5 kg

Certifications: CE, RoHS 2

