


**UFO LED HIGH BAY LIGHT**



Performance High Bay  
Replaces T5, T8 High  
Bay, 400W Metal Halide

LED high bay fixtures are ideal for Warehouses, Manufacturing Facilities, Gymsnasiums, Aviation Hangars, Convention Centers, Big Box Retail Stores, Cold Storage Facilities.



Regular Hanging Mount



Bar Driver Hanging Mount



**Features:**

- Water and Dust Proof (IP65)
- Thin Round Disc Design
- Easy Installation and Maintenance
- 5 Year Warranty
- ETL and DLC Listed
- IP Rating: IP65
- Operating Temperature: -30 to 45°C (-22 to 113°F)
- Humidity: 15% to 90% RH



**Applications:**

- LED high bay fixtures are ideal for Warehouses, Manufacturing Facilities, Gyms, Universities, Aviation Hangars, Convention Centers, Big Box Retail Stores, Cold Storage Facilities.

**Specifications:**


- LED Chip: Lumileds 3030
- Lumen Output: 7,800~32,500LM
- Power: 60/100/120/150/200/250W
- Efficacy (IES): 130lm/w±5%
- Lens options: 60°, 90°, 120°
- Color Temperature: 3000~6500K
- Lumen Maintenance: >50,000 hrs
- Power Factor: >0.9
- Driver: Meanwell
- Weight: 6.6~9.9 lbs
- Mounting Options:
  - Universal hanging bracket
- Material: Die-cast aluminum
- CRI: ≥80
- Input Voltage: 100-277V, 50/60Hz

**Specification:**


WATTS	MODEL	GLOBAL MODEL	LUMENS	LAMP DIMENSION
60W	LK-HB-L1-60W	----	7800lm±5%	10.24"*6.42"
100W	LK-HB-L1-100W	----	13000lm±5%	10.24"*6.42"
120W	LK-HB-L1-120W	----	15600lm±5%	10.24"*6.61"
150W	LK-HB-L1-150W	501755	19500lm±5%	10.24"*6.61"
200W	LK-HB-L2-200W	501756	26000lm±5%	11.8"*6.97"
250W	LK-HB-L2-250W	----	32500lm±5%	11.8"*6.97"



**PACKING INFO**



**Packing Data**



Nominal Wattael	60W	100W	120W	150W	200W	250W
"L" Length "H" Height	286mm/11.3" 204mm/8.0"	286mm/11.3" 204mm/8.0"	286mm/11.3" 204mm/8.0"	286mm/11.3" 204mm/8.0"	336mm/13.2" 210mm/8.3"	336mm/13.2" 210mm/8.3"
Weight	4.5 Kg 9.9 lbs	4.5 Kg 9.9 lbs	5.0 Kg 11.0 lbs	5.0 Kg 11.0 lbs	6 Kg 13.2 lbs	6 Kg 13.2 lbs
20' Qty	1470pcs	1470pcs	1470pcs	1470pcs	1070pcs	1070pcs
40' Qty	3050pcs	3050pcs	3050pcs	3050pcs	2220pcs	2220pcs
40' Hq Qty	3845pcs	3845pcs	3845pcs	3845pcs	2800pcs	2800pcs
45' Hq Qty	4862pcs	4862pcs	4862pcs	4862pcs	3540pcs	3540pcs