

I-BAR SEALERS

W-Series



Ideal for shrink wrapping or making poly bags out of tubing

W-Series I-Bar Sealers are ivory in color and are available in 14", 20", 26", 30", and 35" with a ROUND heating element for cut and seal applications. An optional 2.7mm heating element is available. The sealer is equipped with a film roller, film separator, heat gun holder, and a power outlet. The entire unit is steel constructed (including the work base) for quality and durability. The manufacturer's replacement kit comes with 3 round elements.

Ideal for shrink wrap packaging as the I-Bar Sealers are accompanied with a ROUND element for cut and seal applications

W-Series I-Bar Sealers with Cutters are exactly like the W- Series I-Bar Sealers except the heating element is a flat 2.7mm and there is a sliding cutter attached on the right side of the sealing bar. The blade cuts 0.6" from the seal. The sealers are available in 14", 20", 26", 30", and 35" with a cutting length of 13", 19", 24 1/2", 28 3/4", and 33 3/4" respectively. The manufacturer's replacement kit includes 3 flat heating elements and 1 blade. An optional round heating element for cut and seal is available.

I-bar Sealer w/ cutter has a flat element & sliding blade to make bags out of poly tubing.

	W-350I / W-350IC	W-500I / W-500IC	W-650I / W-650IC	W-750I / W-750IC	W-900I / W-900IC
Power Supply	110V	110V	110V	110V	110V
Power (Watts)	450	600	800	1000	1200
Sealing Length	14"	20"	26"	30"	35"
Cutting Length	13"	19"	24 1/2"	28 3/4"	33 3/4"
Distance from Center of Film to Seal	10.5"	10.5"	10.5"	10.5"	10.5"
Dimensions	23.5" x 16" x 6"	29.5" x 16" x 6"	35" x 16" x 6"	37.5" x 16" x 6"	45" x 16" x 6"
Weight (lbs)	38	44	50	51	65