

# AUTOMATIC FOOT SEALER w/ HEAVY DUTY ELECTROMAGNET

*Model: KS-FS-SERIES*



## Hands Free Operation

- Impulse Sealing – no warm up time needed
- Digital display
- Dual mode operation: auto or manual
- Foot switch allows a hands free operation
- Standalone unit with no need for table top
- Ships via LTL freight only

## More Details:

The KS-FS Series automatic foot impulse sealers are ideal for high volume poly bag and other thermoplastic sealing. This sealer allows you to keep both hands free for quicker and more accurate sealing. The unit operates on impulse sealing and is controlled by a circuit board. The sealer is equipped with a digital display for easy timer settings. Once correct settings have been established, consistent seals will be maintained automatically. The KS-FS series are standalone automatic foot sealer which does not require a tabletop to place the sealer.

Set the sealing (heat), congealing (cool), and recycle (auto) time based on the thickness of your material. Once the settings have been determined, press A/M to initiate the automatic operation of your sealer. The sealer can also operate in manual mode using a foot switch.

Manufacturer's replacement kit includes 2 elements and 1 upper barrier cloth. Work plate also included.

## Specifications:

|              | KS-FS455        | KS-FS605        | KS-FS805        |
|--------------|-----------------|-----------------|-----------------|
| Seal Length  | 17.7"           | 23.6"           | 31.5"           |
| Seal Width   | 5mm             | 5mm             | 5mm             |
| Voltage      | 110V            | 110V            | 110V            |
| Power        | 1050W           | 1300W           | 1500W           |
| Net Weight   | 75lbs           | 83lbs           | 88lbs           |
| Gross Weight | 118lbs          | 130lbs          | 136lbs          |
| Dimensions   | 22" x 21" x 35" | 28" x 22" x 35" | 32" x 24" x 35" |